

W-82 TORX WRENCH SET




- These are long handle Torx wrenches. They are made with the Torx shape on both the long and short end for use in a variety of places.
- The set includes a handy polyurethane holder.

■ Details: T6 / T8 / T10 / T15 / T20 / T25

TORX WRENCH




Part no.	Size	A mm	B mm	Dia shanks mm ϕ	Weight g
W-82-6	T6	15	52	2.5	2
W-82-8	T8	17	59	3	4
W-82-10	T10		67		5
W-82-15	T15	19	72	3.5	7
W-82-20	T20	21	77	4	9
W-82-25	T25	23	83	5	15



W-81 HEX LOBULAR WRENCH SET

■ Weight: 150g



The Contents of Bits

★	★	★	★	★	★	★	★	⊕ No.2X \ominus 6.0mm	⊕ No.1X \ominus 4.5mm
T6	T8	T10	T15	T20	T25	T27	T30		

*Please do not apply torque too much.

D-36 NUT DRIVER SET



- This is a nut driver set with eight interchangeable socket from 4mm to 10mm.
- Included is a convenient and durable cloth pouch.
- Since the case is PVC free it is better for the environment.

■ Contents: 4/4.5/5/5.5/6/7/8/10
 ■ Case Size: 150(W)×100(H)×30(D)mm
 ■ Weight: 280g
 ■ Case Material: Nylon



Size mm	4.0	4.5	5	5.5	6	7	8	10
Head diameter mm ϕ	6.3	7	8.5		9.5	11	12	14
Head depth Dia. mm	10		13					
Length of shanks mm	100							
Dia. of shanks mm ϕ	6.3	7	5					

D-850 NUT DRIVER





- These socket head drivers are designed with a thin outside head.



The D-850-5 is designed to handle a d-sub connector nut.

Part no.	Size of nut mm	O.A.L. mm	Length of shanks mm	Dia. of shanks mm ϕ	Grip Dia. mm ϕ	Head Dia. mm ϕ	Head depth Dia. mm	Applicable nuts	Weight g
D-850-4	4	161	100	3	14	6.5	13	M2	18
D-850-5	5	180		4	21	7.3		M2.5	43
D-850-5.5	5.5					8.5		M3	46
D-850-7	7	215	125	5	26	11.0	18	M4	80
D-850-8	8					12.0		M4.5/M5	83
D-850-10	10					225		5.5	28



CUTTERS
WIRE STRIPPERS
CRIMPERS
TWEEZERS
SCREWDRIVERS & WRENCHES
METAL WORKING TOOLS
CASES & BAGS
TOOL KITS
SOLDERING TOOLS
DESOLDERING TOOLS
MEASURING INSTRUMENTS
MICROSCOPES & MAGNIFIERS
STATIC CONTROL
CLEAN ENVIRONMENT
CHEMICALS
MAINTENANCE TOOLS