



## Worksafe / Worksafe Blue

### Practical, multi-functional mat

- Hardwearing anti-fatigue/anti-slip mat available in two options:
  1. Worksafe
  2. Worksafe Grease-proof (blue)
- Manufactured from a blend of SBR rubber and nitrile.
- Grease-Proof (blue) option especially resilient to grease and aggressive oils.
- Hardwearing, yet comfortable to stand on.
- Reduces the risk of slipping on wet, oily or greasy floors.
- Anti-slip underside to help hold the mat in position.
- Features open drainage holes.
- Moulded bevelled edging all round.

Product height: 15mm

Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
0.9 x 1.5	13	17.5 x 17.5 x 105	Boxed	1	25	Black	SW010001
0.9 x 1.5	13	17.5 x 17.5 x 105	Boxed	1	25	Blue	SW020001

Material:	Worksafe Natural Rubber / Nitrile Rubber Worksafe Blue 38% Nitrile Rubber
Surface Finish:	Textured surface with 22mm holes.
Product Height:	12mm nominal
Operating Temperature:	-20° - +160°C
Resistance to Chemicals:	Natural rubber is resistant to water, and most mild acids.
Environmental Resistance:	Suitable for wet and dry environments.
UV Resistance:	Yes

Typical Applications: Ideal for non-slip and fatigue relief in all industrial areas especially at workstations in machine tool and welding bay environments

Installation Method:	Loose lay
Cleaning Method:	Pressure hose with mild detergent if required.
Product Performance:	

Fatigue:	● ●
Slip Resistance:	● ● ●
Wear:	● ●
Low ≠ High	● → ● ● ● ●

Flame Retardancy:	N/A.
Country of Origin:	Indonesia
Other:	Silicone is used in the production process of the mats and a residue will possibly be left on the product.

End of document

### United Kingdom

COBA Europe Ltd  
Marlborough Drive  
Fleckney, Leicestershire  
LE8 8UR

☎ +44 (0)116 240 1088  
✉ sales@cobaeeurope.com  
🌐 www.cobaeeurope.com

### Germany

COBA Europe GmbH  
Pullenweg 1 - 3  
41352 Korschenbroich

☎ +49 (2161) 2945-0  
✉ verkauf@cobaeeurope.de  
🌐 www.cobaeeurope.de

### Slovakia

COBA Europe s.r.o.  
Terchová - Vyšné Kamenec 11  
SK-013 06

☎ +421 41 507 11 12  
✉ sales@cobaeeurope.sk  
🌐 www.cobaeeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.