
BELKIN®

SOHO Desktop KVM Switch



Share one monitor, keyboard and mouse between up to 4 computers with the re-designed SOHO Desktop KVM Switch

The Belkin SOHO Desktop KVM Switch lets you share one monitor, keyboard and mouse between two or more computers, saving space on your desk and reducing equipment clutter. The sleek, new design incorporates a built-in USB 2.0 2-port hub with one of the ports conveniently located on the front. This is perfect for connecting an MP3 player, printer, scanner or any other of your USB devices to the KVM Switch whilst allowing computers, also connected, to access them. Sensitive push buttons on the front make for easy switching and independent audio-switching allowing you to play music from one computer whilst accessing files from another!





^{**}USB hub available on F1DS10XL and F1DD10XL series only.



The Belkin SOHO Desktop KVM Switch Features:

- Compatible with both Mac® computers and PCs
- Support for hot-key switching for optional switching
- Independent audio switching—Listen to music on one computer whilst you work from a different one connected to the KVM Switch!
- Built-in USB 2.0 2-Port Hub with convenient front access
- Available in VGA or DVI
- PS/2 or USB compatibility
- Cables are included!

BELKIN_®

SOHO Desktop KVM Switch

Package Contents

- SOHO Desktop KVM Switch
- 2/4 All-in-One Cable Kits, 6 ft.
- 9V, 1.1A DC Power Adapter
- User Manual
- Quick Installation Guide



Model depicted above is F1DS104Lea.



SOHO cable kits are included in the box

Product Specifications

i roddet Speemed				
Model No.	F1DS10XJea	F1DS10XLea	F1DD10XLea	
No. of Users Supported	1	1	1	
No. of Computers Supported	2, 4	2, 4	2, 4	
Dimensions	32.7 (L) x 14 (W) x 4.9 (H) cm	32.7 (L) x 14 (W) x 4.9 (H) cm	32.7 (L) x 14 (W) x 4.9 (H) cm	
Weight	1.48 lbs. (.67kg) [2-Port] 1.50 lbs. (.68kg) [4-Port]	1.48 lbs. (.67kg) [2-Port] 1.50 lbs. (.68kg) [4-Port]	1.48 lbs. (.67kg) [2-Port] 1.50 lbs. (.68kg) [4-Port]	
Enclosure	High-impact plastic		, , , , , ,	
Specifications				
Ports	PS/2 and USB	USB	USB	
Monitor Supported	VGA and SVGA MultiSync, LCD	VGA and SVGA MultiSync, LCD	DVI-D	
Max Resolution	2048x1536@85Hz	2048x1536@85Hz	1920x1200	
Audio Input/Output	3.5mm jack			
Microphone Input/Output	3.5mm jack			
Platforms Supported	Mac and PC			
LED Indicator	4 (2-Port), 8 (4-Port)			
KVM Cables Included	Yes			
Power/Environment				
Power Requirements	9V, 1.1A DC adapter with center pin-positive polarity			
Operating Temperature	32° to 104° F (0 to 40° C)			
Storage Temperature	-4° to 140° F (-20 to 60° C)			
Humidity	0-80% RH, non-condensing			
Warranty				
3 years				

Note: Specifications are subject to change without notice.

Part Number	Description	UPC
F1DS102Jea	SOHO 2-Port VGA, PS/2 & USB KVM Switch	7-22868-66465-0
F1DS104Jea	SOHO 4-Port VGA, PS/2 & USB KVM Switch	7-22868-66466-7
F1DS102Lea	SOHO 2-Port VGA & USB KVM Switch	7-22868-67439-0
F1DS104Lea	SOHO 4-Port VGA & USB KVM Switch	7-22868-66467-4
F1DD102Lea	SOHO 2-Port DVI & USB KVM Switch	7-22868-66468-1
F1DD104Lea	SOHO 4-Port DVI & USB KVM Switch	7-22868-66469-8

