

# Product datasheet

Specifications



## "Plain door for PanelSet S3D H600xW400 RAL 7035, with lock"

Local distributor code:

398245768

NSYDS3D64

**EAN Code: 3606480426995**

### Main

Range	PanelSeT
Accessory / separate part category	Enclosure accessory
Product or component type	Door
Application	Multi-purpose
For enclosure nominal dimensions	-
Mounting location	Front
Range compatibility	PanelSeT S3D
Device composition	1 door locking system
Quantity per set	Set of 1

### Complementary

Material	Door: sheet steel
Colour	Grey (RAL 7035)
Surface finish	Textured epoxy polyester
Lock type	Lock 3 mm double bar
Number of locks	1
Door type	Plain
Door opening side	Reversible (120 °)
Maximum load	50 kg/m <sup>2</sup>
Height	Nominal: 600 mm
Width	Nominal: 400 mm
Net weight	2.97 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	41.000 cm
Package 1 Length	61.000 cm
Package 1 Weight	3.974 kg
Unit Type of Package 2	PAM

---

<b>Number of Units in Package 2</b>	50
<b>Package 2 Height</b>	63.000 cm
<b>Package 2 Width</b>	100.000 cm
<b>Package 2 Length</b>	120.000 cm
<b>Package 2 Weight</b>	212.000 kg

---

## Logistical informations

---

<b>Country of origin</b>	FR
--------------------------	----

## Contractual warranty

---

<b>Warranty (in months)</b>	18
-----------------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

## Use Better



### Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

Ba0ee14c-eebb-47d8-a070-ade906247bb0

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Free of Substances of Very High Concern above the threshold](#)

## Use Longer



### Lifetime extension

Repair

No

## Use Again



### Repack and remanufacture

End of life manual availability

No need of specific recycling operations

Take-back

Nej

Image of product / Alternate images

Alternative

---

