

PRODUCT-DETAILS

## CR-U024DC3L

CR-U024DC3L Pluggable interface relay 3c/o, A1-A2=24VDC, 250V/10A, LED



### General Information

Extended Product Type	CR-U024DC3L
Product ID	1SVR405622R1100
EAN	4013614498589
Catalog Description	CR-U024DC3L Pluggable interface relay 3c/o, A1-A2=24VDC, 250V/10A, LED
Long Description	The CR-U024DC3L pluggable interface relay is from the CR-U (universal) relay range. This relay operates with a 24 V DC rated control supply voltage and has 3 c/o (SPDT) output contacts rated at 250 V / 10 A. The relay has an integrated blue test button for manual actuation and locking of the output contacts and an integrated LED. Standard sockets, logic sockets, pluggable function modules, holder and marker are available as accessories.

### Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	85364900

### Popular Downloads

Data Sheet, Technical Information	2CDC110004C0210_05
Instructions and Manuals	1SVC405600M9000

### Dimensions

Product Net Width	35 mm
Product Net Height	54.4 mm
Product Net Depth / Length	35 mm
Product Net Weight	0.083 kg

## Technical

Function	Pluggable universal interface relay CR-U
Sub-Function	Relay with built in LED
Output	3 c/o (SPDT) contacts
Output Signal	250 V / 10 A
Rated Control Supply Voltage (U <sub>s</sub> )	24 V DC

## Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

## Certificates and Declarations (Document Number)

CCC Certificate	CCC_2017010303949759
CQC Certificate	CQC2017010303949759
CSA Certificate	CSA_1587291
Declaration of Conformity - CCC	2020980303000199
Declaration of Conformity - CE	1SVD982021-0003
EAC Certificate	EAC_RU_C-DE.ME77.B.00446-19
Environmental Information	1SAA981009-2401
Instructions and Manuals	1SVC405600M9000
LR Certificate	LR_05_20002_E5
RMRS Certificate	RMRS_1740019250
RoHS Information	1SVD982021-0003
UR Certificate	UR_E244330
VDE Certificate	VDE_40019116

## Container Information

Package Level 1 Units	box 10 piece
Package Level 1 Width	182 mm
Package Level 1 Height	76 mm
Package Level 1 Depth / Length	77 mm
Package Level 1 Gross Weight	0.87 kg
Package Level 1 EAN	4013614374289

## Classifications

Object Classification Code	K
ETIM 4	EC001437 - Switching relay
ETIM 5	EC001437 - Switching relay

ETIM 6	EC001437 - Switching relay
ETIM 7	EC001437 - Switching relay
eClass	V11.0 : 27371601
UNSPSC	39122331
E-Number (Finland)	2712770
E-Number (Sweden)	4005423

---

## Categories

---

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Interface Relays and Optocouplers

