

## Fiber Optic Cable - Multimode Duplex 50/125 - LSZH - LC/ST - 2 m

Product ID: 50FIBLCST2



The 50FIBLCST2 2m LSZH LC to ST Fiber Cable features 50/125 micron fiber for high-speed, high bandwidth data transmissions over Gigabit Ethernet and Fiber Channel networks, with support for duplex multimode applications.

This LC-ST patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 50/125 (OM2) Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability and is backed by our lifetime warranty.

### Certifications, Reports and Compatibility



### Applications

- Use in Gigabit Ethernet and Fiber Channel applications
- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication/Data communication

### Features

- 1x LC MM male connector
- 1x ST MM male connector
- OM2 (50/125) 500MHz multimode fiber
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Attenuation loss meets or exceeds industry standards
- Molded connectors

<b>Hardware</b>	Warranty	Lifetime
	Fiber Size	50/125
	Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
<b>Performance</b>	Cable Rating	1Gbps / 10Gbps
	Fiber Classification	OM2
	Maximum Data Transfer Rate	10Gbps
	Type	Multi Mode
<b>Connector(s)</b>	Connector A	1 - Fiber Optic LC Duplex Male
	Connector B	1 - Fiber Optic ST Duplex Male
<b>Environmental</b>	Humidity	0~90% RH
	Operating Temperature	-20°C to 60°C (-4°F to 140°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
<b>Physical Characteristics</b>	Cable Length	2 m [6.6 ft]
	Color	Orange
	Product Length	2 m [6.6 ft]
	Weight of Product	40 g [1.4 oz]
<b>Packaging Information</b>	Package Height	28 mm [1.1 in]
	Package Length	22 cm [8.7 in]
	Package Quantity	1
	Package Width	20 cm [7.9 in]
	Shipping (Package) Weight	0 kg [0.1 lb]
<b>What's in the Box</b>	Included in Package	1 - 2m Multimode 50/125 Duplex Fiber Patch Cable LC – ST

Product appearance and specifications are subject to change without notice.