



Product datasheet

ENGLISH

Individual Sockets



Specification:

Material: Chrome Vanadium steel

Finished: sandblast w/knurl finished

1/4" drive 6PT socket

RS Stock Number	Global Description
830-3988	1/4" Drive 4mm socket
830-3997	1/4" Drive 4.5mm socket
830-3990	1/4" Drive 5mm socket
830-3994	1/4" Drive 5.5mm socket
830-4007	1/4" Drive 6mm socket
830-4000	1/4" Drive 7mm socket
830-4004	1/4" Drive 8mm socket
830-4013	1/4" Drive 9mm socket
830-4016	1/4" Drive 10mm socket
830-4010	1/4" Drive 11mm socket
830-4029	1/4" Drive 12mm socket
830-4022	1/4" Drive 13mm socket
830-4026	1/4" Drive 14mm socket





ENGLISH

1/2" drive 12 PT socket

RS Stock Number	Global Description
830-4082	1/2" Drive 8mm socket
830-4091	1/2" Drive 9mm socket
830-4094	1/2" Drive 10mm socket
830-4098	1/2" Drive 11mm socket
830-4108	1/2" Drive 12mm socket
830-4101	1/2" Drive 13mm socket
830-4105	1/2" Drive 14mm socket
830-4114	1/2" Drive 15mm socket
830-4117	1/2" Drive 16mm socket
830-4111	1/2" Drive 17mm socket
830-4120	1/2" Drive 18mm socket
830-4123	1/2" Drive 19mm socket
830-4127	1/2" Drive 20mm socket
830-4136	1/2" Drive 21mm socket
830-4139	1/2" Drive 22mm socket
830-4133	1/2" Drive 23mm socket
830-4142	1/2" Drive 24mm socket



3/8" drive 12 PT socket

RS Stock Number	Global Description
830-4035	3/8" Drive 8mm socket
830-4038	3/8" Drive 9mm socket
830-4032	3/8" Drive 10mm socket
830-4041	3/8" Drive 11mm socket
830-4044	3/8" Drive 12mm socket
830-4048	3/8" Drive 13mm socket
830-4057	3/8" Drive 14mm socket
830-4050	3/8" Drive 15mm socket
830-4054	3/8" Drive 16mm socket
830-4063	3/8" Drive 17mm socket
830-4066	3/8" Drive 18mm socket
830-4060	3/8" Drive 19mm socket
830-4079	3/8" Drive 20mm socket
830-4072	3/8" Drive 21mm socket
830-4076	3/8" Drive 22mm socket
830-4085	3/8" Drive 23mm socket
830-4088	3/8" Drive 24mm socket

