

CA-000000090DN - Housing for circular connector



1621410

<https://www.phoenixcontact.com/in/products/1621410>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Housing for circular connector, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, cable diameter range: 3 mm ... 14.5 mm, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1244392

Commercial data

Item number	1621410
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRAEI
GTIN	4046356919357
Weight per piece (including packing)	91.9 g
Weight per piece (excluding packing)	91.9 g
Customs tariff number	85366990
Country of origin	DE

CA-000000090DN - Housing for circular connector



1621410

<https://www.phoenixcontact.com/in/products/1621410>

Technical data

Notes

Order information:	Order contact inserts separately
--------------------	----------------------------------

Product properties

Product type	Circular connector housing
Series	CA
Type	on the cable side

Connector

Housing

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Seal

External cable diameter	3 mm ... 14.5 mm
Seal material	NBR

CA-000000090DN - Housing for circular connector



1621410

<https://www.phoenixcontact.com/in/products/1621410>

Classifications

ECLASS

ECLASS-13.0	27440224
-------------	----------

ETIM

ETIM 9.0	EC003556
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a989f540-1f72-4406-9c9c-c0e3c30fca3b

CA-000000090DN - Housing for circular connector



1621410

<https://www.phoenixcontact.com/in/products/1621410>

Accessories

SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/in/products/1607456>

Torque screwdriver, series: RC, UC, SH, SF



SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/in/products/1607455>

Hook wrench, series: RC, UC, RF, SF



CA-000000090DN - Housing for circular connector



1621410

<https://www.phoenixcontact.com/in/products/1621410>

SF-Z0019 - Protective cap

1607449

<https://www.phoenixcontact.com/in/products/1607449>



Plastic protection cap, with eye, IP40 for connectors with M23 external thread, RF, SF series

RF-Z0014 - Color coding

1620588

<https://www.phoenixcontact.com/in/products/1620588>

Color coding, color: green



CA-000000090DN - Housing for circular connector



1621410


<https://www.phoenixcontact.com/in/products/1621410>

RF-Z0015 - Color coding

1620592

<https://www.phoenixcontact.com/in/products/1620592>

Color coding, color: orange



RF-Z0016 - Color coding

1620593

<https://www.phoenixcontact.com/in/products/1620593>

Color coding, color: black



CA-000000090DN - Housing for circular connector



1621410

<https://www.phoenixcontact.com/in/products/1621410>

RC-Z2469 - Protective cap

1611797

<https://www.phoenixcontact.com/in/products/1611797>



Plastic protection cap, antistatic, for RF, SF, CA, RC series connectors, with M23 external thread

RC-Z2068 - Metal protective cap

1604236

<https://www.phoenixcontact.com/in/products/1604236>



Metal protective cap, M23, series: RC, UC, RF, SF, NC, RM, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241735

CA-000000090DN - Housing for circular connector



1621410

<https://www.phoenixcontact.com/in/products/1621410>

RC-Z2104 - Metal protective cap

1604260

<https://www.phoenixcontact.com/in/products/1604260>



Metal protective cap, M23, series: RC, UC, RF, SF, NC, RM, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241739

PROT-M23PRO-OT-IP20 - Plastic protective cap

1055753

<https://www.phoenixcontact.com/in/products/1055753>



Plastic protective cap, M23, series: M23 PRO

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in