

SOL-ES-BSC-PYR - Sensor

1093211

<https://www.phoenixcontact.com/in/products/1093211>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Lambrecht Meteo GmbH pyranometer for measuring the irradiation intensity in W/m^2 with a 180° aperture opening. The measurement value is provided via Modbus/RTU (RS-485). Corresponds to the accuracy class "First Class" in accordance with ISO 9060

Product description

All "Solarline Environment Sensors" (SOL-ES) are used with the Phoenix Contact weather station via Plug and Play (see accessories). They are especially suitable for capturing weather data in photovoltaic systems.

Corresponding mounting material is available as accessories.

Your advantages

- Includes ISO 9060 testing certificates for the classification First Class
- Corresponds to IEC 61724-1, Class B
- Efficient calibration and maintenance organization

Commercial data

Item number	1093211
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	*****
Product key	DTHAAA
GTIN	4055626911359
Weight per piece (including packing)	700 g
Weight per piece (excluding packing)	700 g
Customs tariff number	90158020
Country of origin	DE

SOL-ES-BSC-PYR - Sensor



1093211

<https://www.phoenixcontact.com/in/products/1093211>

Technical data

Notes

Note regarding documentation	For technical data, see data sheet on the “Downloads” tab
------------------------------	---

Product properties

Product type	Sensor
--------------	--------

SOL-ES-BSC-PYR - Sensor



1093211

<https://www.phoenixcontact.com/in/products/1093211>

Classifications

ECLASS

ECLASS-11.0	27143137
ECLASS-12.0	27143137
ECLASS-13.0	27143137

ETIM

ETIM 9.0	EC000926
----------	----------

UNSPSC

UNSPSC 21.0	43201500
-------------	----------

Environmental product compliance

China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

SOL-ES-BSC-PYR - Sensor

1093211

<https://www.phoenixcontact.com/in/products/1093211>



Accessories

SOL-ES-TRA-1000 - Holder

1074981

<https://www.phoenixcontact.com/in/products/1074981>

Traverse with Lambrecht Meteo GmbH mast holder, length: 1000 mm, comprising anodized aluminum and stainless steel components



SACC-M12MS-5PL M - Connector

1424649

<https://www.phoenixcontact.com/in/products/1424649>



Connector, Universal, 5-position, unshielded, Plug straight M12, coding: A, Push-lock spring connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 4 mm ... 8 mm

SOL-ES-BSC-PYR - Sensor

1093211

<https://www.phoenixcontact.com/in/products/1093211>



SAC-5P-M12MS/ 0,3-PUR/M12FS SH - Sensor/actuator cable

1500884

<https://www.phoenixcontact.com/in/products/1500884>



Sensor/actuator cable, 5-position, PUR halogen-free, black-gray RAL 7021, shielded (Advanced Shielding Technology), Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 0.3 m

SAC-5P-M12MS/ 0,6-PUR/M12FS SH - Sensor/actuator cable

1500897

<https://www.phoenixcontact.com/in/products/1500897>



Sensor/actuator cable, 5-position, PUR halogen-free, black-gray RAL 7021, shielded (Advanced Shielding Technology), Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 0.6 m

SOL-ES-BSC-PYR - Sensor

1093211

<https://www.phoenixcontact.com/in/products/1093211>



SAC-5P-M12MS/ 1,5-PUR/M12FS SH - Sensor/actuator cable

1500907

<https://www.phoenixcontact.com/in/products/1500907>



Sensor/actuator cable, 5-position, PUR halogen-free, black-gray RAL 7021, shielded (Advanced Shielding Technology), Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 1.5 m

SAC-5P-M12MS/ 3,0-PUR/M12FS SH - Sensor/actuator cable

1500910

<https://www.phoenixcontact.com/in/products/1500910>



Sensor/actuator cable, 5-position, PUR halogen-free, black-gray RAL 7021, shielded (Advanced Shielding Technology), Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 3 m

SOL-ES-BSC-PYR - Sensor

1093211

<https://www.phoenixcontact.com/in/products/1093211>



WP-PA HF 13,0 BK - Protective hose

3240681

<https://www.phoenixcontact.com/in/products/3240681>



Protective hose, material: PA 6, UV-resistant: yes, flexible, degree of protection: IP68, color: black, flammability rating in acc. with UL 94: V0, inside diameter: 10 mm, Total length: 50 m

SOL-SC-WTH-STN - Weather station

1322110

<https://www.phoenixcontact.com/in/products/1322110>



Weather station for acquiring measured data from connected environmental sensors. Together with SOL-ES sensors, it can be used in PV parks or other industrial areas, for example. The measured data is made available to the user via a user interface and transmitted to a higher-level data management system.

SOL-ES-BSC-PYR - Sensor

1093211

<https://www.phoenixcontact.com/in/products/1093211>



SAC-5PY-F/M-F VP SH - Y distributor

1419933

<https://www.phoenixcontact.com/in/products/1419933>



Y distributor, 5-position, shielded, Socket straight M12 SPEEDCON, coding: A, on Socket straight M12 SPEEDCON, coding: A and Plug straight M12 SPEEDCON, coding: A, Parallel distributor

SOL-ES-SENSOR-HOLDER-LARGE - Holder

1406811

<https://www.phoenixcontact.com/in/products/1406811>



Sensor bracket from Lambrecht Meteo GmbH, stainless steel, large. Suitable for accommodating certain weather sensors of type SOL-ES, see accessories.

SOL-ES-BSC-PYR - Sensor

1093211

<https://www.phoenixcontact.com/in/products/1093211>



SOL-ES-SENSOR-HOLDER-INCLINED - Holder

1407252

<https://www.phoenixcontact.com/in/products/1407252>



Sensor bracket from Lambrecht Meteo GmbH, stainless steel, angular. Suitable for accommodating certain weather sensors of type SOL-ES, see accessories.

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in