

Features

- Cylindrical cartridge rolls are ideal for removing burrs, smoothing edges, grinding welds, and removing machining marks in hard-to-reach areas such as corners, holes or moulds.
- Its design ensures continuous release of new abrasive grains as the outer layer wears, allowing for precise control of the grinding process.
- Available in various sizes and grits.
- For use with handheld machines (straight grinders or flexible shaft grinders) after mounting on a suitable mandrel.
- Applications:
 - Deburring
 - Cleaning
 - Finishing operations

RS PRO Sanding Drums

RS Stock No.: 0768142, 0768145, 0768147,
0768149



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Cylindrical cartridge rolls are intended for grinding in hard-to-reach places and for deburring castings. They have a multilayer structure; new abrasive grain is exposed when the top layer is worn down. To be used with a straight grinder or drill. Suitable for carbon and stainless steel, aluminium alloys/non-ferrous metals.

General Specifications

Dimensions (Diameter D x Length L x Hole H)	13 mm x 38 mm x 3 mm
Grain Type	Aluminium Oxide (A/O)
Material (Backing/Coating)	Heavy Cotton Cloth / Close coat

Mechanical Specifications

Available Grits	P60, P80, P120, P150
Recommended Mandrel	0768256
Recommended Speed	11,000 min ⁻¹

Grits vs RS Pro Codes

Grits	RS Pro Codes
P60	0768142
P80	0768145
P120	0768147
P150	0768149

Similar Products

Stock No.	Brand	Product Name	Size	Grain Type	Grit	Suitable mandrel
0768260	RS PRO	Cylindrical Cartridge Roll	6x25x3	Aluminium Oxide	60	0768254
0768262	RS PRO	Cylindrical Cartridge Roll	6x25x3	Aluminium Oxide	80	0768254

0768264	RS PRO	Cylindrical Cartridge Roll	6x25x3	Aluminium Oxide	120	0768254
0768266	RS PRO	Cylindrical Cartridge Roll	6x25x3	Aluminium Oxide	150	0768254
0768269	RS PRO	Cylindrical Cartridge Roll	6x38x3	Aluminium Oxide	60	0768256
0768271	RS PRO	Cylindrical Cartridge Roll	6x38x3	Aluminium Oxide	80	0768256
0768274	RS PRO	Cylindrical Cartridge Roll	6x38x3	Aluminium Oxide	120	0768256
0768276	RS PRO	Cylindrical Cartridge Roll	6x38x3	Aluminium Oxide	150	0768256
0768278	RS PRO	Cylindrical Cartridge Roll	8x25x3	Aluminium Oxide	60	0768254
0768280	RS PRO	Cylindrical Cartridge Roll	8x25x3	Aluminium Oxide	80	0768254
0768282	RS PRO	Cylindrical Cartridge Roll	8x25x3	Aluminium Oxide	120	0768254
0768284	RS PRO	Cylindrical Cartridge Roll	8x25x3	Aluminium Oxide	150	0768254
0768107	RS PRO	Cylindrical Cartridge Roll	8x38x3	Aluminium Oxide	60	0768256
0768109	RS PRO	Cylindrical Cartridge Roll	8x38x3	Aluminium Oxide	80	0768256
0768111	RS PRO	Cylindrical Cartridge Roll	8x38x3	Aluminium Oxide	120	0768256
0768113	RS PRO	Cylindrical Cartridge Roll	8x38x3	Aluminium Oxide	150	0768256
0768115	RS PRO	Cylindrical Cartridge Roll	10x25x3	Aluminium Oxide	60	0768254
0768118	RS PRO	Cylindrical Cartridge Roll	10x25x3	Aluminium Oxide	80	0768254
0768120	RS PRO	Cylindrical Cartridge Roll	10x25x3	Aluminium Oxide	120	0768254
0768123	RS PRO	Cylindrical Cartridge Roll	10x25x3	Aluminium Oxide	150	0768254
0768126	RS PRO	Cylindrical Cartridge Roll	10x38x3	Aluminium Oxide	60	0768256
0768127	RS PRO	Cylindrical Cartridge Roll	10x38x3	Aluminium Oxide	80	0768256
0768129	RS PRO	Cylindrical Cartridge Roll	10x38x3	Aluminium Oxide	120	0768256
0768131	RS PRO	Cylindrical Cartridge Roll	10x38x3	Aluminium Oxide	150	0768256
0768133	RS PRO	Cylindrical Cartridge Roll	13x25x3	Aluminium Oxide	60	0768254
0768135	RS PRO	Cylindrical Cartridge Roll	13x25x3	Aluminium Oxide	80	0768254
0768137	RS PRO	Cylindrical Cartridge Roll	13x25x3	Aluminium Oxide	120	0768254

0768140	RS PRO	Cylindrical Cartridge Roll	13x25x3	Aluminium Oxide	150	0768254
---------	--------	-------------------------------	---------	--------------------	-----	---------