



RELOAD 20 Travel

Perfect travel size: Power Bank (20,000 mAh)
Energy on the go – ready to fly

Our RELOAD 20 Travel gives full peace of mind and reliable power on the go by providing enough energy for all USB devices, including mobile phones, tablets and cameras. Incredibly, this power bank also comes pre-charged and can be used immediately, with enough power to charge a smartphone more than 3x. It also comes with a little strap to carry, which is a USB-C cable at the same time.

Suitable for



Product Category

- Power Bank

Technical Specifications

- Suitable for USB device
- Output USB-C2: 4.5 V - 5.0 A / 5.0 V - 4.5 A / 5.0 V - 3.0 A / 9.0 V - 2.0 A / 12.0 V - 1.5 A, 22.5 W (Max)
- Output USB-C cable: 5.0 V - 3.0 A, 9.0 V - 2.22 A, 12.0 V - 1.67 A, 20.0 W (Max)
- Output USB-A: 4.5 V - 5.0 A, 5.0 V - 4.5 A, 5.0 V - 3.0 A, 9.0 V - 2.0 A, 12.0 V - 1.5 A, 22.5 W (Max)
- Total output: 5.0 V - 3.0 A, 15.0 W
- Input USB-C cable: 5.0 V - 3.0 A, 9.0 C - 2.0 A, 12.0 V - 1.5 A, 18.0 W (Max)
- Input USB-C1: 5.0 V - 3.0 A, 9.0 V - 2.0 A, 12.0 V - 1.5 A, 18.0 W (Max)
- Power status: Display

Battery Specifications

- 20,000 mAh, 3.85 V, 2 Batteries, net weight 256 g
- LI-ION, rechargeable
- UN 3480, Dangerous Cargo Class 9

Weight

- Power Bank: 334 g (net)
- Power Bank + packaging: 385 g (gross)
- Master carton: 8400 g (gross)
- Inner carton: 4000 g (gross)

Dimensions

- Power Bank: 112x72x31,8 mm (WxHxD)
- Power Bank + packaging: 185x91x36 mm (WxHxD)
- Master carton: 375x225x220 mm (LxWxH)
- Inner carton: 355x100x200 mm (LxWxH)

Standard Colour

- White

Packaging (Retail)



Description	Article-No.	Sales Unit / Inner / Master carton EAN-Code	Qty per Inner / Master carton / Pal	HS Code	Made in
RELOAD 20 Travel, white	SKPBR20TRA02CN	76403226820635 / 7640326820673 / 7640326820659	10 / 20 / 1200	8507600090	China