

NITREX

Nitrex 247S (247S)

18" (45cm) cut resistant 13 gauge sleeve · cut resistant level E
 Velcro® fastener · thumb slot · soft comfortable knit
 NitreGuard® Technology

Physical Specifications:

Material: Nylon, Polyester,
 HPPE, Glass, Spandex
 Colour: Grey
 One length only: 18" (45cm)

Order Codes | Sizing:


247S | 18"

Packaging:

1 sleeve per polybag
 10 sleeves per master polybag
 3 master polybags per case

Classification:



For more about the **Nitrex** range,
 please **click on the image** 

UNIGLOVES®
NITREX

Features

- Featuring Unigloves NitreGuard Technology
- 13 gauge seamless knitted sleeve with HPPE and encapsulated glass fibre
- Cut resistant level E
- Velcro® fastener
- Thumb slot
- Food approved

Benefits

- Unigloves NitreGuard Technology is awarded to gloves achieving a high-performance in the straight blade cut test
- Seamless knitted sleeve offers unrivalled comfort whilst offering high levels of cut protection to the lower and upper arms
- EN ISO cut level E ($\geq 22N$ & $< 30N$) designed to protect against high level cut hazards
- Velcro fastener allows full adjustability and allows the sleeve to be worn over clothing in cold conditions
- Soft stretchy thumb slot area allows for a comfortable fit under gloves
- Approved for use in food prep and handling

Sectors

- Construction
- Maintenance
- Automotive
- Metal Fabrication
- Glazing
- Construction & Utility
- Engineering and Manufacturing
- Transport and Logistics
- Manufacturing
- Food
- Recycling



VELCRO® is a registered trademark of Velcro Industries B.V.

UNIGLOVES UK
 Registered in England No: 4010200
 VAT registration 791817787

📍 3 Ambley Green, Gillingham Business Park,
 Gillingham, ME8 0NJ, UK
 ☎ +44 (0)800 049 6602
 ✉ enquiries@unigloves.co.uk
 🌐 unigloves.co.uk

UNIGLOVES GERMANY
 Arzt- & Klinikbedarf
 Handelsgesellschaft mbH

📍 Camp-Spich-Straße 71
 D-53842 Troisdorf-Spich,
 ☎ +49 (0) 2241-9323-0
 ✉ unigloves@unigloves.de
 🌐 unigloves.de



Neither this document nor any other statement made herein by or on behalf of Unigloves should be interpreted as a guarantee of marketability or that any Unigloves product is fit for a particular purpose. Unigloves accepts no responsibility for the adequacy or suitability of a user's selection of gloves for their intended application.

Issue No. 1

Prepared at Gillingham
 on 27/10/22