

Features

- For maintenance and general workshop use
- Durable coating and excellent mineral retention means long product life
- Easy to tear backing leaves clean and straight edges
- J-weight cloth gives enhanced flexibility without mineral loss and minimal surface cracking

RS PRO Emery Roll Range

RS Stock No.: 0757808



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Emery Roll

RS PRO industrial quality Emery Rolls range in handy, easy to use brand new dispenser packaging. Premium quality aluminium oxide grain bonded to strong yet easy to tear J-weight cloth backing. Designed for general maintenance work, rust removal, sanding and polishing. Popular for use in the automotive industry.

- *Suitable for use on Rust, Metal, Paint & Non Ferrous*
- *Popular for use in the automotive industry*
- *Premium quality aluminium oxide grain*

General Specifications

| | |
|--------------------------|-------------------|
| Abrasive Material | Aluminium Oxide |
| Sandpaper Type | Emery Cloth Roll |
| Grit Size | See details below |
| Grade | See details below |
| Length | See details below |
| Width | See details below |

| Stock No. | Grit Size | Grade | Length | Width |
|---------------------|-----------|---------------|--------|-------|
| XXX-XXXX 0757806 | 60 | Coarse | 50M | 38mm |
| XXX-XXXX 0757808 | 80 | Medium Coarse | 50M | 38mm |
| XXX-XXXX 0757809 | 120 | Medium | 50M | 38mm |
| XXX-XXXX 0757811 | 180 | Fine | 50M | 38mm |
| XXX-XXXX 0757812 | 280 | Very Fine | 50M | 38mm |
| XXX-XXXX 0757814 | 60 | Coarse | 50M | 50mm |
| XXX-XXXX 0757815 | 80 | Medium Coarse | 50M | 50mm |
| XXX-XXXX 0757816 | 120 | Medium | 50M | 50mm |
| XXX-XXXX 0757817 | 180 | Fine | 50M | 50mm |
| Stock No. | Grit Size | Grade | Length | Width |
| XXX-XXXX | 280 | Very Fine | 50M | 50mm |

| | | | | |
|---------------------|----|--------|-----|------|
| 0757818 | | | | |
| XXX-XXXX 0757806 | 60 | Coarse | 50M | 50mm |

Approvals

| | |
|---------------------|-----------|
| Declarations | REACH DoC |
|---------------------|-----------|

Similar Products

| Stock No. | Brand | Product Name | Grit Size | Grade | Length | Width |
|---------------------|--------|--------------|-----------|------------------|--------|-------|
| XXX-XXXX 0757806 | RS PRO | Emery Roll | 60 | Coarse | 50M | 38mm |
| XXX-XXXX 0757808 | RS PRO | Emery Roll | 80 | Medium Coarse | 50M | 38mm |
| XXX-XXXX 0757809 | RS PRO | Emery Roll | 120 | Medium | 50M | 38mm |
| XXX-XXXX 0757811 | RS PRO | Emery Roll | 180 | Fine | 50M | 38mm |
| XXX-XXXX 0757812 | RS PRO | Emery Roll | 280 | Very Fine | 50M | 38mm |
| XXX-XXXX 0757814 | RS PRO | Emery Roll | 60 | Coarse | 50M | 50mm |
| XXX-XXXX 0757815 | RS PRO | Emery Roll | 80 | Medium Coarse | 50M | 50mm |
| XXX-XXXX 0757816 | RS PRO | Emery Roll | 120 | Medium | 50M | 50mm |
| XXX-XXXX 0757817 | RS PRO | Emery Roll | 180 | Fine | 50M | 50mm |
| XXX-XXXX 0757818 | RS PRO | Emery Roll | 280 | Very Fine | 50M | 50mm |
| XXX-XXXX 0757806 | RS PRO | Emery Roll | 60 | Coarse | 50M | 50mm |