

4-to-1 HDMI Video Switch with Remote Control

Product ID: VS410HDMIE



This 4 port HDMI® Switch lets you connect up to four HDMI-enabled output devices to a single HDMI input - eliminating the need to manually exchange cables to switch between high definition audio video sources.

The HDMI switch fully supports High Speed HDMI device connections, as well as Dolby Digital TrueHD and DTS-HD high definition audio formats and display resolutions up to 1080p(hdtv) / 1920x1200(computer), ensuring a high quality audio and video experience. Suitable for long distance connections, the switch offers a signal enhancement feature that can be used with longer cable connections, boosting the HDMI signal for optimized quality.

The switch provides an economical solution for connecting multiple HDMI out devices (Blu-Ray players, DVD Players, etc.) to a single port on a high definition LCD/Plasma TV.

Certifications, Reports and Compatibility



Applications

- Ideal for home theater situations where you have run out of inputs on your current television to accommodate all of your devices
- Great for use in presentations, trade shows, conferences, retail, and entertainment applications where multiple source devices are required
- Use for video wall setups in retail environments to support several input sources and make them easily switchable
- Perfect for professional A/V test benches testing multiple devices
- Excellent solution for connecting and switching between multiple PCs to one display

Features

- Easy to use remote control for switching between devices
- Supports HDTV resolutions from 480i to 1080p
- Supports PC resolutions from 640x480 to 1920x1200
- High Speed HDMI®, HDCP 1.1, and DVI 1.0 compliant
- Dolby Digital TrueHD and DTS-HD audio

Hardware	Warranty	2 Years
	Audio	Yes
	AV Input	HDMI
	AV Output	HDMI
	Ports	4
Performance	Audio Specifications	Supports Dolby Digital TrueHD and DTS-HD
	Bandwidth	2.25Gbps (Single Link)
	Color Depth	30/36-bit Deep Color
	Maximum Cable Length	65.6 ft [20 m]
	Supported Resolutions	HDTV - 480i~1080p PC - 640x480~1920x1200
Connector(s)	Connector A	4 - HDMI (19 pin) Female
	Connector B	1 - HDMI (19 pin) Female
Power	Center Tip Polarity	Positive
	Input Voltage	110V-240V AC
	Output Current	1A
	Output Voltage	5 DC
	Power Consumption (In Watts)	5
	Power Source	AC Adapter Included
Physical Characteristics	Color	Black
	Enclosure Type	Plastic
	Product Height	1.7 in [44 mm]
	Product Length	9.4 in [240 mm]
	Product Weight	8.5 oz [241 g]
	Product Width	4.1 in [104 mm]
Packaging Information	Shipping (Package) Weight	21.7 oz [616 g]
What's in the Box	Included in Package	1 - HDMI® Video Switch
		1 - IR Remote Control
		1 - Universal Power Adapter (US/UK/EU/AU)
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.