



PRODUCT NUMBER: 1035811  
**Honeywell Avatar OTG Black  
& Red frame / Clear lens /  
Hard Coat**

**Honeywell**

**Overview**

**Reference Number**

1035811

**Product Type**

Eye and Face Protection

**Range**

Spectacles

**Line**

OTG Spectacles

**Brand**

Honeywell

**Industry**

- Automotive and Part Manufacturer
- Building and Construction
- General Industry
- Maintenance

**Features & Benefits**

**Feature**

Weight distribution and stability

**Benefit**

Unlike most OTGs, weight is dispersed throughout the brow and the nose piece

**Feature**

Avatar ultra-adjustable nose piece

**Benefit**

Multi-material nose piece offers 3 vertical positions and flexes to most nose sizes to provide the desired comfort and fit.

**Feature**

Angle-adjustable ratchet temples

**Benefit**

Up to a 15-degree adjustment range for a better fit

**Feature**

Flexible temples MMT+

**Benefit**

Flex system design delivers superior comfort and fit

**Feature**

Insulated wire-core temples

**Benefit**

Increased adjustability, customizability and non-conductivity

**Feature**

Patented indirect venting technology

**Benefit**

Advanced technology that significantly reduces fogging.

**Feature**

Anti-scratch protection

**Benefit**

Excellent scratch resistant hardcoat coating

**Feature**

Multi-Material Technology plus (MMT+)

**Benefit**

Innovative rubber compound provides exceptional grip and comfort

**Technical Description**

**Eyewear Type**

Spectacles

**Shade Lens Color**

Clear

**Lens Coating**

Hard Coat

**Shade Lens Material**

Polycarbonate

**Frame Color**

Black

**Frame Material**

MMT+ Multi-Material Technology Plus

**Body**

MMT+ Multi-Material Technology Plus

**Visible Light Transmission**

>= 85 % ( Greater than or equal to )

**Temple Type**

Insulated Wire core temples

**Nose Pad Design**

Adjustable

**Certifications**

**EU Category PPE**

2

**Quality Assurance**

ISO 9001 / 2000

**EU Certification**

2777\_2\_12145-01\_2\_E00-00 Avatar OTG ID 86025

**Certifications**

- EN 166:2001

**REACH**

<b>EU Regulation 1907/2006 (REACH) Compliance</b>	
The substance(s) listed below may be contained in this product above the threshold level of 0.1% by weight of the listed article.	
<b>Product Reference Sold in Europe</b>	<b>Substance &gt; 0.1%</b>

Substance Name	CAS Number
No Substance Content	

© Honeywell International Inc.