

A-INLE-PG9-N-S - EMC nut



1411276

<https://www.phoenixcontact.com/gb/products/1411276>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

EMC nut, for threads Pg9, color: silver-colored



Commercial data

Item number	1411276
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AF7DZX
Product key	AF7DZX
Catalog page	Page 691 (C-2-2019)
GTIN	4046356924184
Weight per piece (including packing)	3.033 g
Weight per piece (excluding packing)	3.033 g
Customs tariff number	74198090
Country of origin	DE

A-INLE-PG9-N-S - EMC nut

1411276

<https://www.phoenixcontact.com/gb/products/1411276>




Technical data

Product properties

Product type	Flat nut
Thread type	Pg9

Dimensions

Dimensional drawing		
Length	4.7 mm	
Diameter	15.2 mm	
Connecting thread diameter	15.2 mm	
Wrench size, counter nut	18 mm	
Hexagon angular dimension	20 mm	
Thread type connection side	Pg9	

Material specifications

Material	Brass, nickel-plated
----------	----------------------

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-70 °C ... 220 °C

Mounting

Assembly note	for EMC cable glands, for removing a non-conductive surface coating
---------------	---

A-INLE-PG9-N-S - EMC nut


1411276

<https://www.phoenixcontact.com/gb/products/1411276>



Drawings

Dimensional drawing



A-INLE-PG9-N-S - EMC nut



1411276

<https://www.phoenixcontact.com/gb/products/1411276>

Classifications

ECLASS

ECLASS-13.0	27140807
-------------	----------

ETIM

ETIM 9.0	EC000879
----------	----------

UNSPSC

UNSPSC 21.0	31161700
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ebf44e6f-d0ac-4c03-a0f4-7b5a2f788755