

A791 - Mechanics Anti-Vibration Glove

Collection: Mechanic Gloves

Range: Hand Protection

Materials: Nylon, Polyurethane, Polyester, Elastic

Outer Carton: 48

Product information

Experience unparalleled safety and productivity with our cutting-edge anti-vibration glove, expertly designed to reduce the effect of harmful hand arm vibration. Our innovation lies in the shock-absorbing palm material, engineered to deliver exceptional protection without adding bulk. This glove is perfectly suited for professionals who handle jackhammers or concrete breakers and attains an exceptional level of dexterity, reaching the highest rating of level 5.

Mechanic Gloves

Designed to enhance grip for precision work, this collection protects from a broad range of hazards. The gloves are constructed from highly engineered textiles and offer an extensive selection of colours, lining, and size options. This collection is suitable for mechanic applications, general construction, material handling, carpentry and utility work.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5

EN 388: 2016 + A1: 2018 (2322B)

EN 10819:2016 +A1:2019 ((TRm = 0.731 TRh = 0.571))



Features

- Specially designed to reduce the effects of vibration
- For use with jack hammers, concrete breakers
- Wrist strap for secure fitting
- Achieves the highest level of dexterity level 5
- Ideal in construction, joinery and masonry sectors
- Retail tag which aids presentation for retail sales
- CE certified
- UKCA marked
- New style



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A791 - Mechanics Anti-Vibration Glove

Commodity Code: 6116108091

Test House

Cert No: 2777/25868-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
A791K8RS	Black	57.0	35.0	25.0	0.1240	0.0499	5036108414109	15036108899620
A791K8RM	Black	57.0	35.0	25.0	0.1310	0.0499	5036108414093	15036108899613
A791K8RL	Black	57.0	35.0	25.0	0.1400	0.0499	5036108414086	15036108899606
A791K8RXL	Black	57.0	35.0	25.0	0.1530	0.0499	5036108414116	15036108899637
A791K8RXXL	Black	57.0	35.0	25.0	0.1690	0.0499	5036108414123	15036108899644