

Connector Information

Model	Connector Kit Part No.	Location	Mfg. Part No. (Connectors)	Mfg. Part No. (Pins)
GSM7 Series	18-30234-1003	J1	MOLEX: 50-37-5033	MOLEX: 08-70-1040
		J2	MOLEX: 50-37-5023	MOLEX: 08-70-1040
GSC20 Series	18-30234-1004	J1, J2	MOLEX: 50-37-5043	MOLEX: 08-70-1040
GSx25 Series	18-30234-3206	J1	AMP: 640250-3	AMP: 770522-1
		J2	AMP: 640250-6	AMP: 770522-1
GSM28 Series	18-30234-3104 (3-pin input)	J1	AMP: 640250-5	AMP: 770522-1
		J2	AMP: 640250-4	AMP: 770522-1
GPx40 Series Single Output	18-30234-3106	J1	AMP: 640250-3	AMP: 770522-1
		J2	AMP: 640250-6	AMP: 770522-1
		J3	AMP: 640442-2	N/A
		Gnd	MOLEX: AA-5261	N/A
GPx40 Series Multiple Output	18-30234-3006	J1	AMP: 640250-3	AMP: 770522-1
		J2	AMP: 640250-6	AMP: 770522-1
		Gnd	MOLEX: AA-5261	N/A
GPx41 Series	18-30234-3004	J1	AMP: 640250-2	AMP: 770522-1
		J2	AMP: 640250-4	AMP: 770522-1
GPC50 Series	18-30234-5003	J1	MOLEX: 09-50-8031	MOLEX: 08-50-0189
		J2, J3, J4	MOLEX: 22-01-1042	MOLEX: 08-50-0114
		Gnd	MOLEX: AA-5261	N/A
GPx55 Series	18-30234-3009	J1	AMP: 640250-5	AMP: 770522-1
		J2	AMP: 640250-9	AMP: 770522-1
GPx80 Series	18-30234-3013	J1	AMP: 640250-5	AMP: 770522-1
		J2	AMP: 1-640250-3	AMP: 770522-1
GPx130/140 Series	18-30234-3016	J1	AMP: 640250-2	AMP: 770522-1
		J2	AMP: 640440-4	N/A
		J3	AMP: 1-640250-6	AMP: 770522-1
GLC40 Series	18-30234-3206	J1	Gnd	AMP: 770522-1
		J2	AMP: 640250-6	AMP: 770522-1
GLC50 Series	18-30234-3006	J1	AMP: 640250-3	AMP: 770522-1
		J2	AMP: 640250-6	AMP: 770522-1
		Gnd	MOLEX: AA-5261	N/A
GLx65 Series Single Output	18-30234-3106	J1	AMP: 640250-3	AMP: 770476-1
		J2	AMP: 640250-6	AMP: 770476-1
		J3	AMP: 640440-2	
		Gnd	MOLEX: AA-5261	
GLx65 Series Multiple Output	18-30234-3006	J1	AMP: 640250-3	AMP: 770476-1
		J2	AMP: 640250-6	AMP: 770476-1
		Gnd	MOLEX: AA-5261	
GLC75 Series Single Output	18-30234-3009	J1	AMP: 640250-5	AMP: 770522-1
		J2	AMP: 640250-9	AMP: 770522-1
GLC75 Series Multiple Output & GLC110 Series Multiple Output	18-30234-3013	J1	AMP: 640250-5	AMP: 770522-1
		J2	AMP: 1-640445-3	AMP: 770522-1
GPFx110 Series	18-30234-3109 (with fan connector)	J1	AMP: 640250-5	AMP: 770522-1
		J2	AMP: 640250-9	AMP: 770522-1
		J3	AMP: 640442-2	N/A
GPFC160 Series	18-30234-3116 (with fan connector)	J1	AMP: 640250-5	AMP: 770522-1
		J2	AMP: 640440-4	N/A
		J3	AMP: 1-640250-6	AMP: 770522-1
		Fan	AMP: 640442-2	N/A

Connector Information

Model	Power Supply End	Location	Manufacturer	System End	Tools
NMX-350/500	770743-1	J1	AMP	770580-1 With Sockets 171639-1	90760-1
NMX-750	770974-1	J6	AMP	770583-1 With Sockets 171639-1	
NMX-1000/MAX-1000	350830-1	J2	AMP	350736-1 With Pins 350918-3	90299-2
MAX-1000	03-06-1062	J3	MOLEX	03-06-2061 With Pins 02-06-2132	11-01-0037
RMX/TMX	PLC30M400A1-168.3	J1	POSITRONIC	PCL30F300A1-168.4 PLC30F1000 With FC114N2 Pins	
NMX-350/500	MTA 640456-2	J3	AMP	Use close end with polarizing tabs 643816 For AWG 28 643815 For AWG 26 643814 For AWG 24 643813 For AWG 22 Add "number of Circuits" to Type Number	Handle 58074-1 Tool 58246-1
DMX-500	MTA 640456-2	J3	AMP		
DCX/MAX	MTA 640456-4	J1	AMP		
NMX-750	MTA 640456-5	J1	AMP		
NMX-350	MTA 640458-6	J2	AMP		
NMX-500	MTA 640456-8	J2	AMP		
NMX-1000	MTA-640456-9	J3	AMP		

OLDER MODELS	Connector Kit Part No.	Location	Mfg. Part No. (Connectors)	Mfg. Part No. (Pins)
VBA Series	18-30234-3306 (3-pin input)	J1	AMP: 640250-5	AMP: 770522-1
		J2	AMP: 640250-6	AMP: 770522-1
VCA326 Series	18-30234-5003	J1	MOLEX: 09-50-8031	MOLEX: 08-50-0189
		J2, J3, J4	MOLEX: 22-01-1042	MOLEX: 80-50-0114
		E1 (Gnd)	MOLEX: AA-5261	MOLEX: N/A
VCA4xx Series	18-30234-3010	J1	MOLEX: 09-50-8051	MOLEX: 08-50-0189
		J2	MOLEX: 09-50-8101	MOLEX: 08-50-0189
		E1 (Gnd)	MOLEX: AA-5261	MOLEX: N/A