




Mounting kit for LOGO! and SIPLUS LOGO!

4TE / 8 TE with keys

These mounting kits facilitate quick and easy front panel installation of LOGO! and SIPLUS LOGO! type products, up to a front plate thickness of 8 mm. Thanks to the plexiglass screen and panel seals, the devices are shielded, even in harsh environments, up to protection class IP65. The keys integrated into the front panel enable acknowledgement of the messages without having to remove the front screen.

The SIPLUS extreme product range provides different logic modules for extreme temperature ranges, and for use in adverse conditions involving pollution gas atmospheres or condensation.

The advantages at a glance

- Simple, fast assembly for front panels
- Protection class IP65 with front screen
- Protection class IP30 without front screen
- Integral keys for acknowledging messages
- Lightweight:
approximately 150 g (4PU) and 170 g (8PU)
- Suitable for front plate thickness to 8 mm
- Frame color adapted to LOGO! (anthracite)



Optimal for every requirement – Features and options

	Possible configurations	Scope of supply	Order numbers ¹⁾	Typical installations
Mounting kit 4PU	1 LOGO! (6ED1052-...) or 1 SIPLUS LOGO! (6AG1052-...)	Frame with seal, 4 knurled screws, 2 clips, Front screen with keys	6AG1057-1AA00-0AA3	 Mounting kit 4PU with LOGO!
Mounting kit 8PU	1 LOGO! (6ED1052-...) or 1 SIPLUS LOGO! (6AG1052-...) with 2 LOGO! expansion modules (6ED1055-...) or 2 SIPLUS LOGO! expansion modules (6AG1055-...) or 1 basic module and up to 2 expansion modules (maximum width: 144 mm)	Frame with seal, 1 mounting piece (1 PU), 3 covers (1 PU), 4 knurled screws, 2 clips, Front screen with keys	6AG1057-1AA00-0AA2	 Mounting kit 8PU with LOGO! 1 expansion module

When installing several devices in one mounting kit, it is necessary to brace them on the rear with a shared DIN rail (length of DIN rail = maximum width – 10 mm).

You can download the installation dimensions from the [Siemens Online Support:](https://support.automation.siemens.com/WW/view/en/56228406)
<https://support.automation.siemens.com/WW/view/en/56228406>

¹⁾ Current ordering data, plus terms and conditions of sales and delivery can be found on the Internet at: www.siemens.com/industrymall

Siemens AG
Digital Factory Division
Factory Automation
Postfach 48 48
90026 Nürnberg
Germany

Subject to change without prior notice
PDF (6ZB5131-0AW02-0BA1)
BR 0718 PDF 2 De
Produced in Germany
© Siemens AG 2018

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract. Availability and technical specifications are subject to change without notice.
All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.