



1507

Air

Peli™ Air cases are the first in a series of remarkable innovations engineered by Peli, the pioneers of protective cases. For over 45 years Peli has designed and crafted the most influential protective cases in the world, and we're just getting started.

With the launch of the Peli™ Air line of cases, we're redefining the future of protection with a remarkable union of light and tough.

- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Fold down over-molded handle
- Stainless steel padlock protectors
- Press and Pull™ Latches
- Limited Lifetime Warranty
- Super-light proprietary HPX²™ Polymer - up to 40% lighter
- Waterproof O-ring seal
- User-customizable Pick N Pluck™ foam
- Waterproof, crushproof, dustproof
- IP67 & MIL-SPEC certified



CONFIGURATIONS



1507
Standard



1507NF
No Foam



1507WD
With Padded Dividers



1507TP
With TrekPak Divider System



1507WF
With Foam

DIMENSIONS

Interior (L×W×D)	15.15 x 11.38" x 8.52 (38.5 x 28.9 x 21.6 cm)
Exterior (L×W×D)	16.87 x 14.10" x 9.27 (42.8 x 35.8 x 23.5 cm)
Lid Depth	2.03" (5.2 cm)
Bottom Depth	6.49" (16.5 cm)
Total Depth	8.52" (21.6 cm)
Int Volume	0.85 ft ³ (0.024 m ³)
Padlock Hole Diameter	0.31" (0.8 cm)

MATERIALS

Body	Proprietary Polypropylene Blend
Latch	ABS
O-Ring	EPDM
Purge Body	ABS
Purge Vent	Hi-Flow Gore-Tex 3 Micron Hydrophobic Non-Woven

COLOURS

 Black	 Orange	 Silver	 Yellow
---	--	--	--

WEIGHT

Weight With Foam	6.43 lbs (2.92 kg)
Weight Empty	5.24 lbs (2.38 kg)
Buoyancy	54.00 lbs (24.49 kg)
Master Pack Weight	14.78 lbs (6.7 kg)

TEMPERATURE

Minimum Temperature	0°F (-17.8 °C)
Maximum Temperature	140°F (60 °C)

ACCESSORIES

			
1506TSA TSA Lock	1500D Desiccant Silica Gel	1507AirDS Padded Divider Set	1507AirFS 5 pc. Replacement Foam Set

Peli
c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999
info@peli.com • www.peli.com

Document created on 08-19-26