

# C-RC 150/M16 DIN - Ring cable lug



3240130

<https://www.phoenixcontact.com/gb/products/3240130>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ring cable lug, non-insulated, 150 mm<sup>2</sup>, M16

## Your advantages

- The CRIMPFOX-RC... tools from our CRIMPFOX range of crimping pliers are available for optimum crimping
- The hard-soldered press zone enables maximum conductor pull-out values to be achieved
- The ring cable lugs without plastic sleeve are made from high-quality tin-plated electrolytic copper for maximum protection against corrosion

## Commercial data

Item number	3240130
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BH3422
Product key	BH3422
Catalog page	Page 491 (C-3-2019)
GTIN	4046356453479
Weight per piece (including packing)	78.75 g
Weight per piece (excluding packing)	74.75 g
Customs tariff number	85369010
Country of origin	CN

# C-RC 150/M16 DIN - Ring cable lug

3240130

<https://www.phoenixcontact.com/gb/products/3240130>




## Technical data

### Product properties

Product type	Connector
Product property	Design according to DIN 46234
	Brazed
	Tin-plated

### Dimensions

Dimensional drawing	
Width	30 mm
Sleeve length	65 mm
Length of the insulating material sleeve	24 mm
Maximum stripping length	27 mm
Distance from the center to the insulating material sleeve	26 mm
Min. material thickness	3.2 mm
Inner dimensions of the insulating collar	19 mm

### Internal dimensions

Internal diameter	17 mm
-------------------	-------

### Material specifications

Color	silver-colored
Material	Copper
Coating	tin-plated

### Mechanical properties

#### Technical data

Sleeve length	65 mm
---------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	110 °C
---------------------------------	--------

### Standards and regulations

Design according to standard	DIN 46234
------------------------------	-----------

# C-RC 150/M16 DIN - Ring cable lug

3240130

<https://www.phoenixcontact.com/gb/products/3240130>



## Drawings

Dimensional drawing



# C-RC 150/M16 DIN - Ring cable lug



3240130

<https://www.phoenixcontact.com/gb/products/3240130>

## Classifications

### ECLASS

ECLASS-13.0	27400204
-------------	----------

### ETIM

ETIM 9.0	EC001052
----------	----------

### UNSPSC

UNSPSC 21.0	27121700
-------------	----------

# C-RC 150/M16 DIN - Ring cable lug



3240130

<https://www.phoenixcontact.com/gb/products/3240130>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)