



FOAM MODULE 4/3 22 OPEN PIPE WRENCHES 6/12 SIDE SATIN CHROME

93-J22MM

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:52:26





DESCRIPTION

FOAM MODULE 4/3 22 OPEN PIPE WRENCHES 6/12 SIDE SATIN CHROME

Foam module with 22 through box spanners (93-...) ideal for all industrial applications. The 22 through box spanners are designed with 6/12-flat configurations for maximum adaptability, covering a range of sizes going from 8 to 32 mm. The spanners offer an elegant satin chrome finish that is corrosion resistant while ensuring a non-slip grip and exceptional durability. The spanners are stored in a made-to-measure foam tray.

SPECIFIC DATA

Designation	FOAM MODULE 4/3 22 OPEN PIPE WRENCHES 6/12 SIDE SATIN CHROME
Sales reference	93-J22MM
Weight (kg)	9.88

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>



Width (mm)	410
Length (mm)	550
Height (mm)	50
Guarantee	O SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

>> [Find out more](#)

Toolset



x 22

Through box wrenches, 6/12-flat, satin finish, in mm

93-...

Ref : 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 23 - 24 - 26 - 27 - 28 - 29 - 30 - 32



x 1

EMPTY 3/3 FOAM MODULE FOR COMPOSITION 94-SDJ22MM N°1 8-28

MODM-119-1

Ref : MODM-119-1



x 1

EMPTY 1/3 FOAM MODULE FOR COMPOSITION 94-SDJ22MM N°2 29-32

MODM-119-2

Ref : MODM-119-2

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

