



1000V INSULATED WRENCH MODULE

CP-44ZPM

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:58:58





DESCRIPTION

1000V INSULATED WRENCH MODULE

SPECIFIC DATA

Designation	3/3 FOAM MODULE WITH 44 KEYS, 1000 VOLTS
Sales reference	CP-44ZPM
Weight (kg)	6.06
Guarantee	O SAM TOOL guarantee.

Guarantee applied

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:58:58



O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

Toolset

	x 1	1000 v insulated adjustable wrenches Z-54-... Ref : Z-54-8
	x 14	1000 v insulated offset ring wrenches Z-105-... Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 16 - 17 - 18 - 19 - 21 mm
	x 6	OPEN-ENDED WRENCH WITH RATCHET 1 INSULATED Z-11-... Ref : 8 - 10 - 13 - 16 - 17 - 19 mm
	x 14	1000 v insulated open end wrenches Z-10-... Ref : 8 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 24 mm
	x 4	1000 v insulated 90° elbow hexagonal wrenches Z-65-... Ref : 3 - 4 - 5 - 6 mm
	x 4	1000 v insulated open socket wrenches Z-80-... Ref : 8 - 10 - 13 - 17 mm
	x 1	1000 v insulated cross wrench Z-87-6-12 Ref : 6x8x10x12 mm

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:58:58

