



SETRON, cylindrical fuse link, 14x51 mm, 6 A, gG, Un AC: 690 V

Figure similar

| Model                                                                               |  |                          |             |
|-------------------------------------------------------------------------------------|--|--------------------------|-------------|
| product brand name                                                                  |  | SETRON                   |             |
| product designation                                                                 |  | Cylindrical fuse link    |             |
| General technical data                                                              |  |                          |             |
| operating class of the fuse link                                                    |  | gG                       |             |
| type of voltage of the operating voltage                                            |  | AC                       |             |
| supply voltage at DC                                                                |  | 250 V                    |             |
| Dissipation                                                                         |  |                          |             |
| power loss [W]                                                                      |  | 1.5 W                    |             |
| power loss [W] for rated value of the current at AC in hot operating state per pole |  | 2 W                      |             |
| Main circuit                                                                        |  |                          |             |
| operational current rated value                                                     |  | 6 A                      |             |
| Product details                                                                     |  |                          |             |
| product component striker                                                           |  | No                       |             |
| Mechanical Design                                                                   |  |                          |             |
| mounting position                                                                   |  | Any, preferably vertical |             |
| net weight                                                                          |  | 21 g                     |             |
| Approvals Certificates                                                              |  |                          |             |
| General Product Approval                                                            |  | other                    | Environment |




[Confirmation](#)



[Environmental Confirmations](#)

| Further information                                                                                                                                                   |  |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| Information on the packaging                                                                                                                                          |  |
| <a href="https://support.industry.siemens.com/cs/ww/en/view/109813875">https://support.industry.siemens.com/cs/ww/en/view/109813875</a>                               |  |
| Information- and Downloadcenter (Catalogs, Brochures,...)                                                                                                             |  |
| <a href="http://www.siemens.com/lowvoltage/catalogs">http://www.siemens.com/lowvoltage/catalogs</a>                                                                   |  |
| Industry Mall (Online ordering system)                                                                                                                                |  |
| <a href="https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW6101-1">https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW6101-1</a> |  |
| Service&Support (Manuals, Certificates, Characteristics, FAQs,...)                                                                                                    |  |
| <a href="https://support.industry.siemens.com/cs/ww/en/ps/3NW6101-1">https://support.industry.siemens.com/cs/ww/en/ps/3NW6101-1</a>                                   |  |
| Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)                                                                       |  |
| <a href="http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6101-1">http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6101-1</a>                 |  |
| CAx-Online-Generator                                                                                                                                                  |  |
| <a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>                                                                                                   |  |
| Tender specifications                                                                                                                                                 |  |
| <a href="http://www.siemens.com/specifications">http://www.siemens.com/specifications</a>                                                                             |  |



---

last modified:

4/11/2025 

