# Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



# Thalassa PHD outdoor heavy duty roof ventilation module H95 W500 D420 - IP55

Local distributor code: 402657352

NSYPCVR54HD

! Discontinued on: 9 Feb 2023

(!) Discontinued

EAN Code: 3606480680922

## Main

| Range                              | Thalassa                                 |  |
|------------------------------------|--|--|
| Application                        | Outdoor heavy duty                       |  |
| Accessory / separate part category | Enclosure accessory                      |  |
| Product or component type          | Ventilated roof                          |  |
| Device application                 | Multi-purpose                            |  |
| Mounting location                  | On top of enclosure                      |  |
| Range compatibility                | Thalassa Thalassa PHD suitable enclosure |  |
| Quantity per set                   | Set of 1                                 |  |

# Complementary

| Material                | Steel with anti-corrosive coating                                     |  |
|-------------------------|---|--|
| Colour                  | Grey (RAL 7035)   |  |
| Surface finish          | Polyester powder  |  |
| Fixing mode             | By screws and claws (x2) - screw type M6 - roof fixing point location |  |
| Corrosion resistance    | 90100 % conforming to ISO 12944 C4H                                   |  |
| Height                  | 95 mm   |  |
| Width                   | 500 mm  |  |
| Depth                   | 420 mm  |  |
| IP degree of protection | IP55 conforming to IEC 60529  |  |

# **Packing Units**

| Unit Type of Package 1       | PCE       |
|------------------------------|-----------|
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 52.000 cm |
| Package 1 Width              | 45.500 cm |
| Package 1 Length             | 13.500 cm |
| Package 1 Weight             | 6.482 kg  |
| Unit Type of Package 2       | P12       |
| Number of Units in Package 2 | 10        |
| Package 2 Height             | 85.000 cm |

| Package 2 Width  | 80.000 cm  |
|------------------|------------|
| Package 2 Length | 120.000 cm |
| Package 2 Weight | 75.000 kg  |

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

### Environmental Data explained >

How we assess product sustainability >

# ☑ Environmental footprint

Environmental Disclosure

Product Environmental Profile

### **Use Better**

| Packaging made with recycled cardboard | No   |
|--|--|
| Packaging without single use plastic   | No   |
| EU RoHS Directive                      | Pro-active compliance (Product out of EU RoHS legal scope) |
| SCIP Number                            | 1341ad4e-77b9-40e3-bab0-32043fbc5959                       |
| REACh Regulation                       | REACh Declaration  |

### **Use Again**

| ○ Repack and remanufacture |  |
|----------------------------|--|
| Circularity Profile        | No need of specific recycling operations |
| Take-back                  | No                                       |