

Previously known as: AlphaTec® 1500 - Model 138

Comfortable protection from hazardous particulates in general industrial environments..

DESIGN

Asbestos fibres, such as Chrysotile, are typically 3-5 microns in size. The SMS fabric used in the construction of MICROGARD® 1500 coveralls has been proven to filter 100% of particles larger than 3 microns.

STITCHED SEAMS

Combining strength with particle barrier

SUIT FEATURES

- 3 piece hood
- Elasticated hood, wrists, waist and ankles
- 2-way front zipper with resealable storm flap

COLOURS

White, Navy & Orange

SIZES

S-6XL



Industries

- Machinery and Equipment
- Construction
- Chemical

Applications


- Inspection (picking, checking and marking)
- Asbestos Related Work
- Handling of powders
- General maintenance

KEY FEATURES & BENEFITS


- Protection - Proven to filter 100% of particles >3 microns*
- Comfort - Air and water vapour permeable (breathable) to help reduce the risk of heat stress
- Silicone Free - critical in spray painting applications
- Optimised body fit - improves wearer comfort and safety

* KAKEN Particle penetration test

Material Diagram



Seam Diagram



Performance Standards



0598

EN ISO 13688:2013



TYPE 5



TYPE 6



EN 1073-2

Product Information

Product Information	
Available Sizes	S, M, L, XL, 2XL
Color	White, Orange, Navy
Country Of Origin	Bangladesh, China, Sri Lanka
Models Available	113
Packaging Overview	Individually Packed
Product Material	SMS fabric
Product Reference	1500 - Model 138
Seam Type	Stitched
Shelf Life	5 years
Style Number	W15S138, O15S138, N15S138

Suit components & accessories

Suit Components and Accessories	
Design Features	Coverall, 3-piece hood, elasticated hood, wrists, waist and ankles. 2-way front zipper with re-sealable storm flap.

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

