



Switches > Tactile Switches



Contact Current Rating: **50 mA**  
 Actuator Style: **Rectangular Actuator**  
 Operating Function: **Off (On)**  
 Contact Base Material: **Brass**  
 Switch Contact Plating Material: **Silver**

### Features

#### Product Type Features

Illuminated	With
Actuator Style	Rectangular Actuator

#### Configuration Features

Operating Function	Off (On)
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single

#### Body Features

Actuator Force	100 g[3.52 oz]
Product Orientation	Vertical
Actuator Color	Brown

#### Contact Features

Contact Current Rating	50 mA
Contact Base Material	Brass
Switch Contact Plating Material	Silver

#### Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

#### Housing Features

--	--



Process Sealed	No
----------------	----

**Usage Conditions**

Operating Temperature Range	-25 – 70 °C
-----------------------------	-------------

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**



TE Part # 5-2213819-3  
6X6 ILL TACT SMT 520GF SOFT ORANGE



TE Part # 2-2213819-9  
6X6 ILL TACT SMT 160GF HI SOFT ORANGE



TE Part # 4-2213819-5  
6X6 ILL TACT SMT 260GF HI SOFT ORANGE



TE Part # 2-2213819-3  
6X6 ILL TACT SMT 160GF RED



TE Part # 4-2213819-8  
6X6 ILL TACT SMT 260GF HI COLD  
WHITE

### Also in the Series | [Alcoswitch FSMIJ](#)




[Tactile Switches\(128\)](#)


### Customers Also Bought



TE Part #1-2213818-5  
6X6 ILL TACT THT 100GF HI RED



TE Part #324001  
SPLICE,SOLIS BUTT STRAP 24-20



TE Part #CAT-L489-CH8172  
LEAVYSEAL Connector Housings



TE Part #346108-000  
S02-13-R




TE Part #5-1418363-1  
39 POS TAB 2.8x0.8 HEADER CODE



TE Part #CAT-C339-H85913  
Power Resistors: Aluminum Housed,  
HSA



TE Part #4-1579001-3  
ERGO DIE MCP 1,2 LL



TE Part #DTM04-3P-KIT  
DTM04-3P AND WEG ONLY

### Documents

#### Product Drawings

[6X6 ILL TACT THT 100GF YELLOW GREEN](#)

English

#### CAD Files

[3D PDF](#)

[3D](#)



**Customer View Model**

[ENG\\_CVM\\_CVM\\_2213818-3\\_B.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_2213818-3\\_B.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_2213818-3\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Datasheets & Catalog Pages**

[SWITCHES\\_CORE\\_PROGRAM\\_CATALOG](#)

English