

V-Gard® Frames & Accessories

Face Protection - Technical Data Sheet



The V-Gard standard frame works ideally with any MSA slotted helmet and the wide choice of V-Gard visors. With the unique sloped frame design material slides off the frame and out of site. With the unique 3-point visor loading visors are fitted and removed quickly. The V-Gard standard frame exists in a special elevated temperature version, made of nylon, and that withstands temperatures of 176.7°C without warping, cracking or crazing.

The V-Gard universal frame provides the highest quality protection while making use and installation easier than ever. Designed to easily attach accessories to MSA's industry safety helmets without any disassembly.

V-Gard frames are compatible with MSA visors and other above-the-neck industrial helmet accessories. They can be worn with or without ear-defenders and are perfectly compatible with many half-mask respirators and more.

MSA's unique debris control can be easily added to any V-Gard frame to create a tight seal between helmet and frame.

V-Gard frames and the optional debris control are certified with V-Gard visors to ensure protection against impacts, molten metal and electrical risks. Please ask for the separate datasheets on visors and chin protectors.

V-Gard frames are certified in use with V-Gard®, V-Gard 200, V-Gard 500/520, ThermalGard, V-Gard 930, V-Gard 950 and V-Gard 950 class 2.



P/N	Description	Weight (g)	EN166 Marking
V-Gard Standard Frames and spare parts			
10121266	V-Gard standard frame, black (HDPE)	105	389 BT / EN1731-F
10115730	V-Gard standard frame, with debris control, black (HDPE)	136	389 BT / EN1731-F
10121267	Elevated Temperature ET standard frame for slotted helmets, grey (PA Nylon)	97	389 BT / EN1731-F
10116539	Replacement debris wiper for V-Gard standard frame, spare	10	N/A
10117496	Replacement slot adaptors for V-Gard standard frame, spare (2 pairs)	8	N/A
V-Gard Universal Frames and spare parts			
10190640	V-Gard universal frame, black (HDPE)	150	389 BT / EN1731-F
10190639	V-Gard universal frame with debris control, black (HDPE)	160	389 BT / EN1731-F
10187163	Replacement debris wiper for V-Gard Universal frame, spare	10	N/A
10187251	Replacement rubber strap for V-Gard universal frame, spare	28	N/A
Packaging	Specified part numbers correspond to each individual product, which is individually packed in polybag with instruction and individual label with barcode EAN code 13. MSA sells in Masterpacks of 10. Masterpack label includes GS1-128 code.		



10121266 – V-Gard Standard frame for slotted helmets



10115730 – V-Gard Standard frame for slotted helmets with debris control



10121267 – V-Gard Standard frame ET (Elevated Temperature)



10190640 – V-Gard Universal Frame



10190639 – V-Gard Universal Frame with debris control

Note: This Bulletin contains only a general description of the products shown. While product uses and performance capabilities are generally described, the products shall not, under any circumstances, be used by untrained or unqualified individuals. The products shall not be used until the product instructions/user manual, which contains detailed information concerning the proper use and care of the products, including any warnings or cautions, have been thoroughly read and understood. Specifications are subject to change without prior notice. MSA is a registered trademark of MSA Technology, LLC in the US, Europe, and other Countries. For all other trademarks visit <https://us.msasafety.com/Trademarks>.

MSA operates in over 40 countries worldwide. To find an MSA office near you, please visit [MSAsafety.com/offices](https://us.msasafety.com/offices).