

Cutting

1. DREMEL® EZ SpeedClic™: Starter Set and Cutting Wheels



SC406 SC409 SC456 SC456B

DREMEL EZ
SpeedClic

Dremel, the inventor of the EZ SpeedClic quick-change system for rotary tool accessories, now offers an extended line of EZ SpeedClic metal cutting accessories. The Starter Set SC406 includes the unique EZ SpeedClic mandrel and two fiberglass reinforced metal cutting wheels. The SC456, SC456B and SC409 are replacement metal cutting wheels, whereby the SC409 wheels have a thickness of just 0,75 mm.



Model	Quantity	Working Ø mm	Shank Ø mm	Ordernumber	EAN
SC406	2	38,0	3,2	2615S406JC	8710364042814
SC409	5	38,0	3,2	2615S409JB	8710364042869
SC456	5	38,0	3,2	2615S456JC	8710364042821
SC456B	12	38,0	3,2	2615S456JD	8710364042845

2. DREMEL® EZ SpeedClic™: Plastic Cutting Wheels 5-Pack



SC476

DREMEL EZ
SpeedClic

These cutting wheels are specially designed for cutting in all sorts of plastics. Quick, Easy, Keyless.



Model	Quantity	Working Ø mm	Shank Ø mm	Ordernumber	EAN
SC476	5	38,0	3,2	2615S476JB	8710364042852

Cutting

3. DREMEL® EZ SpeedClic™: Wood Cutting Wheel



SC544

DREMEL EZ
SpeedClic

Cut faster through wood. With this ø 38 mm EZ SpeedClic wood cutting wheel 544 you can cut both hard and soft types of wood and also laminate. The carbide coating makes this wheel very durable. Quick, Easy, Keyless.



Model	Quantity	Working Ø mm	Shank Ø mm	Ordernumber	EAN
SC544	1	38,0	3,2	2615S544JB	8710364042876

4. DREMEL® EZ SpeedClic™: Diamond Cutting Wheel



SC545

DREMEL EZ
SpeedClic

A unique accessory designed for cutting hard materials. For example concrete, stone, porcelain, ceramic and hard epoxies. The diamond wheel produces a fine cut, is extremely durable, does not break and retains its shape. Quick, Easy, Keyless.



Model	Quantity	Working Ø mm	Shank Ø mm	Ordernumber	EAN
SC545	1	38,0	3,2	2615S545JB	8710364042883

Cutting

5. Cut-Off Wheels



409 420 426 540

For slicing and cutting in metal, wood and plastic. Cut-off wheels make it easy to cut or slot bolts, screws, sheet metal, thin wood and plastic. Fiberglass reinforced cut-off wheels (456, 426, 426B) are for tough applications. The cut-off wheel cuts only along its edge. Do not attempt to sand or cut curved holes. Use Dremel cut-off wheels with mandrel 402.



Model	Quantity	Working Ø mm	Shank Ø mm	Ordernumber	EAN
409	36	24,0	3,2	2615040932	8710364007424
420	20	24,0	3,2	2615042032	8710364007431
426	5	32,0	3,2	2615042632	8710364007448
540	5	32,0	3,2	2615054032	8710364010516

6. Cutting/Shaping Wheel



542

The ultimate solution for wood. The special design of the cutting/shaping wheel 542 ensures that you can cut both hard and soft types of wood, cut grooves and shape wood. The carbide coating makes the wheel especially durable.



Model	Quantity	Working Ø mm	Shank Ø mm	Ordernumber	EAN
542	1	25,4	3,2	2615054265	8710364017119

Cutting

7. Rip/Cross-Cut Blade



546

Precision saw blade for fine, clean and straight cuts in all sorts of wood. Perfect for laminate and wood flooring or thin wood plates. Use only with Dremel Mini Saw attachment 670. Made of carbon steel, 48 offset teeth guarantee precise, fast cuts up to 6.35 mm.



Model	Quantity	Working Ø mm	Shank Ø mm	Ordernumber	EAN
546	2	31,8	3,2	26150546JB	8710364045143

8. Spiral Cutting Bits



561

562

The multipurpose cutting bit 561 cuts wood, plastic, fiberglass, drywall, laminate & vinyl siding. The tile cutting bit 562 cuts ceramic wall tile, cement board and plaster. (Not for use on floor tile)



Model	Quantity	Working Ø mm	Shank Ø mm	Ordernumber	EAN
561	3	3,2	3,2	26150561JA	8710364045150
562	1	3,2	3,2	2615056232	8710364010608

Cutting

9. Grout Removal Bits



Ideal for cleaning wall and floor grout or removing grout to replace broken tiles. Use with the Dremel Grout Removal attachment 568.



Model	Quantity	Working Ø mm	Shank Ø mm	Ordernumber	EAN
569	1	1,6	3,2	2615056932	8710364014125
570	1	3,2	3,2	2615057032	8710364016624