

3530 // NYLOFLEX

Assembly gloves
PPE risk category II



100% recycled polyester
Very high abrasion resistance
Very good dry and oil grip

3530 // NYLOFLEX



Material:	Polyester, recycled, grey
Coating:	Nitrile, sanded, black
Size(s):	7-12
Packaging unit:	144 pair(s)
Certification:	EN 388

NITRAS NYLOFLEX, assembly gloves, grey, nitrile coating, black (colour code: 1210), sanded, partly coated on palm and fingertips, knitted wrist, 100% recycled Polyester, NITRAS NOW, very slip resistant, perfect grip, very high abrasion resistance, very good dry and oil grip, PPE risk category II

EN 388

EN ISO 21420



4131X

15
GAUGE



NITRAS
NOW

Size	7	8	9	10	11	12
Colour coding system						

Industries

-  Craft
-  Building / Construction
-  Automotive manufacturing
-  Commissioning / shipping
-  Landscape gardening

Advantages

- + 100% recycled polyester
- + Very high abrasion resistance
- + Very good dry and oil grip



Performance values

EN 388:2016 + A1:2018	Test parameter	Performance levels	Test result
 4131X	Abrasion resistance	1-4	4
	Blade cut resistance (Coupe-Test)	1-5	1
	Tear resistance	1-4	3
	Puncture resistance	1-4	1
	Blade cut resistance (TDM)	A-F	X
EN ISO 21420:2020	Test parameter	Performance levels	Test result
	Dexterity	1-5	5

Additional information

	Material	Colour
Palm	Nitrile, sanded, on recycled polyester	black
Index finger and thumb	Nitrile, sanded, on recycled polyester	black
Back of the hand	Polyester, recycled	grey
Fingertips	Nitrile, sanded, on recycled polyester	black
Cuff / knitted wrist	Polyester, recycled	grey

Logistics data

Size	GTIN (SPU)	GTIN (PU)	Length (m)	Width (m)	Height (m)	Weight (kg)	Quantity PU / pallet
7	4059904217140	4059904217195	0,42 m	0,41 m	0,26 m	8,04 kg	
8	4059904217157	4059904217201	0,41 m	0,4 m	0,27 m	8,98 kg	
9	4059904217164	4059904217218	0,42 m	0,41 m	0,27 m	10,2 kg	
10	4059904217171	4059904217225	0,47 m	0,45 m	0,29 m	11,45 kg	
11	4059904217188	4059904217232	0,42 m	0,28 m	0,42 m	12 kg	
12	4059904217249	4059904217256	0,44 m	0,3 m	0,44 m	12,5 kg	

Customs tariff number: 61161020910

Country of origin: China