

## Features

- Delivers clean, straight cuts in metal pipes and closed profiles.
- Made from fully hardened, high-grade High-Speed Steel (HSS), it features a fine 2mm tooth pitch and a long 132mm blade length, designed to cut medium-thickness pipes and profiles with wall thicknesses of 2.5–6mm and diameters up to 65mm.

## Jigsaw Blade –Metal T318B –Standard Cut

RS Stock No.: 0757840



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS PRO Jigsaw Blade

0757840 Standard for Metal Jigsaw Blade delivers clean, straight cuts in metal pipes and closed profiles. Made from fully hardened, high-grade High-Speed Steel (HSS), it features a fine 2mm tooth pitch and a long 132mm blade length, designed to cut medium-thickness pipes and profiles with wall thicknesses of 2.5–6mm and diameters up to 65mm.

- *Wavy Set Teeth for fine, straight cutting*
- *Suitable for use on Mild Steel, Sheet Steel, High Grade Steel & Steel Pipes*
- *Bayonet (T-Shank) fitting system compatible with all popular brands of bayonet fitting machines*
- *Supplied in 5pc Packs*

## General Specifications

<b>Tooth Design</b>	Wavy Set, Milled
<b>Type</b>	Jigsaw Blade
<b>Teeth Spacing</b>	2.0mm
<b>Cut Depth</b>	<65mm
<b>Cut Type</b>	Standard Cutting
<b>Material</b>	High Speed Steel
<b>Fitting</b>	Bayonet (T-Shank)
<b>Length</b>	132mm

Stock No.	Cut Type	Teeth Spacing	Length	Tooth Design
XXX-XXXX 0757836	Standard Cutting	1.1-1.5mm	77mm	Wavy Set, Milled
XXX-XXXX 0757837	Standard Cutting	1.9-2.3mm	77mm	Wavy Set, Milled
XXX-XXXX 0757838	Standard Cutting	0.7mm	77mm	Wavy Set, Milled
XXX-XXXX 0757839	Standard Cutting	1.2mm	132mm	Wavy Set, Milled
XXX-XXXX 0757840	Standard Cutting	2.0mm	132mm	Wavy Set, Milled
XXX-XXXX 0757842	Special Cutting	3.0mm	100mm	Side Set, Milled

## Approvals

<b>Declarations</b>	REACH DoC
---------------------	-----------

## Similar Products

Stock No.	Brand	Product Name	Cut Type	Teeth Spacing	Length	Tooth Design
XXX-XXXX 0757836	RS PRO	Jigsaw Blade	Standard Cutting	1.1-1.5mm	77mm	Wavy Set, Milled
XXX-XXXX 0757837	RS PRO	Jigsaw Blade	Standard Cutting	1.9-2.3mm	77mm	Wavy Set, Milled
XXX-XXXX 0757838	RS PRO	Jigsaw Blade	Standard Cutting	0.7mm	77mm	Wavy Set, Milled
XXX-XXXX 0757839	RS PRO	Jigsaw Blade	Standard Cutting	1.2mm	132mm	Wavy Set, Milled
XXX-XXXX 0757840	RS PRO	Jigsaw Blade	Standard Cutting	2.0mm	132mm	Wavy Set, Milled
XXX-XXXX 0757842	RS PRO	Jigsaw Blade	Special Cutting	3.0mm	100mm	Side Set, Milled

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories