


## 64382 HLX-A 200-15

Halogen lamps, current-controlled with PK30d base



### Areas of application

- Airfield lighting

### Product benefits

- Reduced operation and maintenance costs due to long life time
- Instant and constant light output over the lamp life
- Flicker-free operation
- Mercury-free

### Product features

- Dimmable
- Available with connector combinations A, B, C/Z on request
- Infrared radiation output that provides light in the worst of conditions



## Technical data



### Electrical data

Nominal voltage	30.3 V
Nominal wattage	200.00 W
Nominal current	6.60 A

### Photometrical data

Nominal luminous flux	4800 lm
-----------------------	---------

### Dimensions & weight



Product line drawing

Base

Diameter	13.5 mm
Length	57.0 mm

### Lifespan

Lifespan	1500 h
----------	--------

### Additional product data

Base (standard designation)	PK30d
-----------------------------	-------

### Country specific categorizations

Order reference	64382 HLX-A 200
-----------------	-----------------

## Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
--------------	------------	---------	------------	--------

## Product datasheet

---

4008321345738	OSRH64382HLX	-	-	-
---------------	--------------	---	---	---

---

## Product datasheet

---

### Safety advice

---

To prevent personal injury or damage to property, halogen lamps may only be operated in suitable luminaires designed with suitable mechanisms (protective shields, grids, etc.) to ensure that in the event of a lamp bursting no parts/shards can escape and that during operation no ultraviolet radiation can escape. There must also be a warning sign to indicate that the lamps give off high levels of heat. Detailed information is available on request.

---

### Logistical Data

---

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321345738	64382 HLX-A 200-15	Folding carton box 1	37 mm x 33 mm x 71 mm	0.09 dm <sup>3</sup>	23.00 g
4008321345745	64382 HLX-A 200-15	Shipping carton box 100	154 mm x 191 mm x 341 mm	10.03 dm <sup>3</sup>	2300.00 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### References / Links

---

For more information on airfield lamps see the brochure:

"The reliable guiding stars - Effective solutions for airfield lighting: Tungsten halogen lamps and LED light sources".

---

### Disclaimer

---

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

---