

DCS572P2-QW

18V XR Brushless 184 mm Rail Compatible Circular Saw - 2 x 5Ah



5035048729205



Product Description :

A high-performance, cord-free 184mm circular saw, compatible with The DEWALT® Rail System and designed for woodworking specialists. With its highly-efficient DEWALT Brushless motor, the DCS572 combines extended runtime and dependability with the freedom of powerful cordless operation, cutting up to 20 linear metres of 50mm softwood on a single charge (with a 18V XR 5.0Ah battery). A straightforward saw-to-rail adjustment mechanism ensures the saw can be installed to give an accurate and smooth cut on every job, while the onboard tool storage and spindle lock permit the blade to be changed quickly, as soon as required.

Product Features and Benefits :

- 18V XR BRUSHLESS MOTOR: Enhanced efficiency and durability.
- 3 YEAR GUARANTEE: Tool covered by extended warranty, subject to registration.
- PART OF THE CORDLESS 18V XR SYSTEM: Fully Compatible With 250+ Solutions.
- Includes heavy-duty TSTAK kit box allowing different combinations with other TSTAK storage units.
- GUIDE RAIL COMPATIBLE: Quick and easy use with the DEWALT guide rail system for perfectly straight cuts.
- MAX DEPTH OF CUT: 184mm blade delivers 58mm at 90°
- VERSATILE: Bevel capacity up to 57 degrees.
- TOOL FREE ADJUSTMENT: Quick and easy adjustment of depth and bevel settings.
- BRIGHT LED: For improved cut line visibility.
- ADDITIONAL CONTROL AND WORK SAFETY: Provided by lock off switch and electronic motor brake.
- DIRECT COMPATIBILITY WITH AIRLOCK SYSTEM: Ensuring easy and secure connection with DEWALT dust extractors for high dust-extraction efficiency and increased user health protection.
- BUILT IN DUST BLOWER: Clears dust and debris from the cut line for increased accuracy.

Technical specifications :

- Battery Capacity : 5 Ah
- Power Output : 900 W
- Sound Pressure : 94.00 dB(A)
- Blade Bore [Metric] : 16 mm
- Blade Diameter [Metric] : 184 mm
- Sound Power : 102 dB(A)
- Uncertainty K (Vibration) : 1.5 m/s²
- Sound Pressure Uncertainty : 3 dB(A)
- Sound Power Uncertainty : 3 dB(A)

Product Warranty :

1 Year Limited Warranty, 3 Year Limited Warranty When Registered

Included items :

- 18V XR Brushless 184 mm Rail Compatible Circular Saw (x1)
- 184 mm 24-Tooth TCT Saw Blade (x1)
- Blade Wrench (x1)
- Rip Fence (x1)
- Dust Extraction Port (x1)
- 5 Ah Battery With State of Charge Indicator (x2)
- 4 A Multi-Voltage Charger (x1)

