

PRODUCT-DETAILS

# P9MCC

## TOGGLE SWITCH P9MCC



### General Information

Extended Product Type	P9MCC
Product ID	1SFA184697R9006
EAN	7320500522578
Catalog Description	TOGGLE SWITCH P9MCC
Long Description	TOGGLE SWITCH 3-POSITION MOMENTARY/MAINTAINED BLACK

### Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	8536501990

### Popular Downloads

Data Sheet, Technical Information	1SFC151007C02_
Instructions and Manuals	1SFC151011M0201

### Dimensions

Product Net Width	29.7 mm
Product Net Height	44.5 mm
Product Net Depth /	62.1 mm

Length	
Product Net Weight	0.073 kg

## Technical

Color	Black
Actuator Type	Toggle switch
Bezel Material	Satin Chrome Metal
Illumination	Non-illuminated
Function	Momentary/Maintained
Sub-Function	3-position
Sub-Function 2	CAM B
Maintained Positions	B, C
Spring Return From	A to B
Degree of Protection	Front IP66
Enclosure Type NEMA	Type1 Type12 Type13 Type3 Type3R Type3S Type4 Type4X

## Environmental

RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Information	2CMT2019-005862
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business

## Certificates and Declarations (Document Number)

BV Certificate	2CMT2019-005867
CB Certificate	2CMT2019-005872
CSA Certificate	2CMT2019-005868
Declaration of Conformity - CE	2CMT2019-005862
DNV GL Certificate	2CMT2019-005876
Instructions and Manuals	1SFC151011M0201
RINA Certificate	2CMT2019-005866
RoHS Information	2CMT2019-005862
UL Certificate	2CMT2019-005868

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	41 mm
Package Level 1 Depth / Length	80 mm
Package Level 1 Height	41 mm
Package Level 1 Gross Weight	0.073 kg
Package Level 1 EAN	7320500522578

---

**Classifications**

---

ETIM 7	EC000222 - Front element for selector switch
eClass	V11.0 : 27371213
UNSPSC	39121500
E-Number (Finland)	2314705
E-Number (Sweden)	3705886

---

---

**Categories**

---

Low Voltage Products and Systems → Control Products → Pilot Devices → Modular Metal Range P9M

