



SERIES S1 POWERFUL IMPACT WRENCH 1/2"

RC2780

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:38





DESCRIPTION

SERIES S1 POWERFUL IMPACT WRENCH 1/2"

PRACTICAL: Tightening / loosening reversal with one pushbutton, 3 tightening speeds and 1 loosening speed. **COMFORT:** Two-material handle for better comfort / suspension ring.

Compact wrench for intensive use for industrial and automotive maintenance jobs. Low-consumption wrench. Double hammer punch, low vibrations. Three-position torque variator and control button on the front. Suspension ring.

POWERFUL

Its so-called "cold" motor develops optimum power of 1,350 Nm when full-power unscrewing is required.

The power developed represents an improvement of at least 25% with respect to what commonly exists for 1/2" wrenches.

Compact wrench for intensive maintenance jobs, and also for automotive applications: exhaust, drivetrain.

Low-consumption wrench. Double-hammer punch, reducing the vibrations. Cold-insulating S1 casing (handhold and wrench balancing...).

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:38



3-Position variable torque control and sensitive-touch control button at the front. Suspension ring.

STANDARDS / DIRECTIVES

2006/42/CE

SPECIFIC DATA

Designation	IMPACT WRENCH 1/2"
Sales reference	RC2780
L (mm)	193
Weight (g)	2420
Rotation speed (rpm)	10 000
Vibration (m/s ²)	5,4
Noise level (dBa)	85
C mm	6,5
C min mm	400
C mm	1/4
Maximum input torque Nm	1 350
Hammer type	
Guarantee	M2 SAM Equipment and Machine Guarantee

Guarantee applied

M2 | SAM Equipment and Machine Guarantee

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>



[>> Find out more](#)

PNEUMATIC

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:38

