

**New**

# Kaldvik








7329A2ET2



**SIOPOR<sup>®</sup>**  
EXCELL

## Hi-vis rain jacket with ARC protection

A light jacket that offers you a very high level of protection, including ARC protection, is that possible? Yes it is. Our hi-vis Kaldvik rain jacket is made out of the new lightweight (280 g/m<sup>2</sup>) SIOPOR<sup>®</sup> Excell fabric and complies to many international standards like IEC 61482-2, EN ISO 11612, EN ISO 11611, EN 13034 and EN 1149-5 amongst others. Thanks to our I.L.S. system different linings can be zipped in this soft and supple jacket. Furthermore, the Kaldvik has many practical features like the possibility of attaching a hood (available separately), narrowing the sleeve ends, 1 chest pocket, 2 inside pockets and a practical zipper grip for easily opening and closing the jacket.

|   |  |   |  |   |  |  |
|---|--|---|--|---|--|--|
| <br><b>IEC 61482-2:</b><br>2018<br><b>APC1</b><br>ATPV 9,1 cal/cm <sup>2</sup> | <br><b>EN ISO 11612:</b><br>2015<br>A1 A2 B1 C1 E1 F1 | <br><b>EN ISO 11611</b><br>2015<br>Class 1 - A1/A2 | <br><b>EN 1149-5:</b><br>2018 | <br><b>EN 13034:</b><br>2005 +A1:2009<br>Type PB [6] | <br><b>EN ISO 20471:</b><br>2013 +A1:2016 | <br><b>EN 343:</b><br>2019<br>4<br>4<br>x |
|---|--|---|--|---|--|--|

# Hi-vis rain jacket with ARC protection

**Kaldvik - 7329A2ET2**

## European Standards: (based upon size L)

- » IEC 61482-2 : 2018 APC1 - ATPV 9.1 cal/cm<sup>2</sup>
- » EN ISO 11612 : 2015 / A1 A2 B1 C1 E1 F1
- » EN ISO 11611 : 2015 / Class 1 - A1 A2
- » EN 1149-5 : 2018
- » EN 13034 : 2005 + A1 : 2009 Type PB [6]
- » EN ISO 20471 : 2013 +A1 2016 / Class 3
- » EN 343 : 2019 / Class 4-4-X
- » EN ISO 13688 : 2013

## Exterior:

- » Straight collar
- » Provided for hood (hood available separately)
- » Zip closure under flap with touch & close fastening
- » 1 patched chest pocket
- » 2 patched pockets
- » 2 loops for gas detectors
- » Round sleeves
- » Sleeve narrowing by press studs
- » Drawstring in hem
- » Slide-in zipper system for extra ease of use
- » Flame retardant reflective tape (50mm)
- » Back length 85 cm (L)

## Interior:

- » Unlined
- » 2 inside pockets
- » Different linings/fleeces can be zipped in

## Fabric:

SIOPOR® Excell: 3-layer fabric: Dobby ripstop polyester fabric (& AST) + breathable FR PU + inherent FR knitting; ± 280 g/m<sup>2</sup>

## Sizes:

S - XXXL

## Colour:

- » 278 Hi-Vis Yellow/Navy
- » 279 Hi-Vis Orange/Navy

## Combining products:

7203 – 7204 – 7276

## I.L.S.:

7690 – 7870 – 9375 – 9376 – 9633 – 9634 – 9643 – 9644 – 9705 – 9896

## Packaging:

5 pieces per box

## Wash and care instructions:



### SIOEN head office

Fabriekstraat 23  
B-8850 Ardoonie  
Belgium

T: +32 (51) 740 800

F: +32 (51) 740 962

[www.sioen-ppc.com](http://www.sioen-ppc.com)



Discover  
our products

© 2020 Sioen Apparel - Protection through Innovation, Flexothane®, Siopor® and the SIOEN logo are trademarks of the Sioen Industries Group.

Please note that all information given in this document is intended to be useful and informative and is correct to the best of our knowledge at time of print. No liability can be accepted for inaccuracies or omissions. The right is reserved to amend this information without prior notice. All our technical files, style descriptions, presentations, designs and drawings, give the latest update of the standards and design or style features of each product. However, delivered products may comply with previous standards, design or style features. For that Sioen disclaims any liability whatsoever. Contact our sales for full information if specific requirements are needed.