

Crimping pliers - CRIMPFOX-C120 - 1212318

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Basic pliers, for accommodating dies for a wide range of type of contacts up to 120 mm²

Your advantages

- Wide variety of available dies
- A mechanical drive system keeps the level of force required to an absolute minimum
- Easily foldable jaw holders mean that the dies can be changed quickly
- A mechanical drive system keeps the level of force required to an absolute minimum
- Easily foldable jaw holders mean that the dies can be changed quickly

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 454643
GTIN	4046356454643

Technical data

Dimensions

Length (b)	430 mm
Width (a)	130 mm
Height (c)	65 mm

General

Color	black
Compression	universal
Min. cross section	6 mm ²
Max. cross section	120 mm ²
AWG min	10
AWG max	3/0
Weight	2000 g

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Crimping pliers - CRIMPFOX-C120 - 1212318

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 11.0	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Crimping pliers - CRIMPFOX-C120 - 1212318

Approvals

EAC



RU x-
DE.xx08.B.02974

Accessories

Accessories

Die

Replacement die - CRIMPFOX-C120 AI 70/M-DIE - 1212335



Die (upper part), for CRIMPFOX-C120, for ferrules (DIN 46228) 70 mm², trapeze crimp

Replacement die - CRIMPFOX-C120 AI 95/M-DIE - 1212336



Die (upper part), for CRIMPFOX-C120, for ferrules (DIN 46228) 95 mm², trapeze crimp

Replacement die - CRIMPFOX-C120 AI 50/F-DIE - 1212337



Die (lower part), for CRIMPFOX-C120, for ferrules (DIN 46228) 50 mm², trapeze crimp

Replacement die - CRIMPFOX-C120 AI 70/F-DIE - 1212338



Die (lower part), for CRIMPFOX-C120, for ferrules (DIN 46228) 70 mm², trapeze crimp

Crimping pliers - CRIMPFOX-C120 - 1212318

Accessories

Replacement die - CRIMPFOX-C120 AI 95/F-DIE - 1212339



Die (lower part), for CRIMPFOX-C120, for ferrules (DIN 46228) 95 mm², trapeze crimp

Replacement die - CRIMPFOX-C120 RCI 10/DIE - 1212327



Die (pair), for CRIMPFOX-C120, for insulated ring cable lug 10 mm², oval crimp

Replacement die - CRIMPFOX-C120 RCI 16/DIE - 1212328



Die (pair), for CRIMPFOX-C120, for insulated ring cable lug 16 mm², oval crimp

Replacement die - CRIMPFOX-C120 RCI 25/DIE - 1212329



Die (pair), for CRIMPFOX-C120, for insulated ring cable lug 25 mm², oval crimp

Replacement die - CRIMPFOX-C120 RCI 35/DIE - 1212330



Die (pair), for CRIMPFOX-C120, for insulated ring cable lug 35 mm², oval crimp

Crimping pliers - CRIMPFOX-C120 - 1212318

Accessories

Replacement die - CRIMPFOX-C120 RC 70/M-DIE - 1212331



Die (upper part), for CRIMPFOX-C120, for non-insulated cable lugs (DIN 46234) 6 ... 70 mm², indent crimp

Replacement die - CRIMPFOX-C120 RC 35/F-DIE - 1212332



Die (lower part), for CRIMPFOX-C120, for non-insulated cable lugs (DIN 46234) 10 + 16 + 25 + 35 mm², indent crimp

Replacement die - CRIMPFOX-C120 RC 50/F-DIE - 1212333



Die (lower part), for CRIMPFOX-C120, for non-insulated cable lugs (DIN 46234) 6 + 50 mm², indent crimp

Replacement die - CRIMPFOX-C120 RC 70/F-DIE - 1212334



Die (lower part), for CRIMPFOX-C120, for non-insulated cable lugs (DIN 46234) 10 + 70 mm², indent crimp

Replacement die - CRIMPFOX-C120 RCT 35-1/DIE - 1212320



Die (pair), for CRIMPFOX-C120, for copper tube lug 16 + 35 mm², WM crimp

Crimping pliers - CRIMPFOX-C120 - 1212318

Accessories

Replacement die - CRIMPFOX-C120 RCT 50-1/DIE - 1212321



Die (pair), for CRIMPFOX-C120, for copper tube lug 25 + 50 mm², WM crimp

Replacement die - CRIMPFOX-C120 RCT 70-1/DIE - 1212319



Die (pair), for CRIMPFOX-C120, for copper tube lug 10 + 70 mm², WM crimp

Replacement die - CRIMPFOX-C120 RCT 95-1/DIE - 1212322



Die (pair), for CRIMPFOX-C120, for copper tube lug 95 mm², WM crimp

Replacement die - CRIMPFOX-C120 RCT 120-1/DIE - 1212323



Die (pair), for CRIMPFOX-C120, for copper tube lug 120 mm², WM crimp

Replacement die - CRIMPFOX-C120 R25-50/DIE - 1212324



pre-round die (pair), for CRIMPFOX-C120, for sector cable 25 + 50 mm²

Crimping pliers - CRIMPFOX-C120 - 1212318

Accessories

Replacement die - CRIMPFOX-C120 R35-70/DIE - 1212325



pre-round die (pair), for CRIMPFOX-C120, for sector cable 35 + 70 mm²

Replacement die - CRIMPFOX-C120 R95/DIE - 1212326



Pre-round die (pair), for CRIMPFOX-C120, for sector cable 95 mm²

Phoenix Contact 2022 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>