

TECHNICAL SPECIFICATION



EVOGuard®M Forestry Helmet Systems

EVOGuard®M3 Forestry Helmet System - with Throat Cover & Sun Cape / AKE24E-200-800



DESCRIPTION

The EVOGuard®M Forestry browguard and helmet systems are innovative solutions to protect the wearer in a multitude of high risk working environments. All EVOGuard® visor components are fully compatible with a range of existing EVO® helmet models.

OPTIONS

EVOGuard®M3 Forestry Helmet System (AKE24A-500-800)

**EVOGuard®M3 Forestry Helmet System - with Throat
Cover & Sun Cape (AKE24E-200-800)**

EVOGuard®M2 Forestry Helmet System (AKE24A-400-800)

SAFETY STANDARDS

EN 397 • EN 352-3 • EN 1731 • EN 166



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jspsafety.com / Web: www.jspsafety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jspsafety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.


Page 1 of 3 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.



SPECIFICATIONS

	Peak Standard		Impact Resistance 50 Joules
	Lateral Deformation Yes		Molten Metal Yes
	Maximum Temperature +50°C		Minimum Temperature -40°C
	ABS Shell Yes		Textile Harness
	Depth Adjustment 3D Harness		Wheel Ratchet Yes
	Ventilation No		Reflective Option Fitted
	Integrated Eyewear Fitted		ID card holder Optional
	Optional 2 point chinstrap (EN397 & EN 812 compliant) Optional		Optional 4 point chinstrap (EN397 Compliant) Fitted
	Mounting Helmet		SNR 31 dB
	Cup Material ABS		Adjustable Yes
	Hygiene Hygiene Kit		Manufacturer's Trademark JSP Dagger
	Low Energy Impact resists a 6 mm, 0.86g ball @ 45 m/s ° Maximum protection for glasses F		Visible Light Transmittance (VLT) 80%
	Visor Length 18cm		Material ABS Frame and Woven Stainless Steel Mesh Visor
	BSI Kitemark Yes		Recyclable Yes
	JSPCheck Yes		Product Weight 809g

FEATURES



Visor Range

Two high performance complete forestry systems are available, enabling users to select the perfect visor for their task and price point.



Dual Layer Protection

The EVOGuard®M Forestry Helmet and Forestry Browguard Systems both feature a secondary layer of eye protection in the form of the integrated EVOSpec® polycarbonate retractable eyeshield.



Balanced & Secure

Fitted to a browguard or helmet, the self-lubricating nylon hinges hold the visor securely in position even during extreme movement, whilst offering balanced, even weight distribution.



Product Compatibility

Designed to maximise compatibility with a broad range of JSP products, such as the Force®8 respirator with PressToCheck™, Springfit™ disposable masks and the Sonis® helmet mounted ear defender range.



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jspafety.com / Web: www.jspafety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jspafety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 2 of 3 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.





Supreme Comfort

Features an easy to use Revolution® wheel ratchet and a 3D-Adjustment harness, which offers 1-2-3 point depth settings for increased adaptability to ensure a perfect, secure fit.



Coverage

EVOGuard® visors provide comprehensive facial coverage without limiting movement or vision.

LOGO

☒ Front

RANGE



DOWNLOADS

-  [Image Pack \(ZIP\)](#)
-  [doc-evoguard.pdf \(PDF\)](#)



JSP Limited. Worsham Mill. Minster Lovell. Oxford OX29 0TA. England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jspsafety.com / Web: www.jspsafety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jspsafety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 3 of 3 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.

