

# QPD PSK 3/4X1,5 - Protective cap



1414724

<https://www.phoenixcontact.com/gb/products/1414724>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective cap plastic, for QPD-QUICKON connection 3(4)x 1.5 mm<sup>2</sup>, IP50

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 1414724             |
| Packing unit                         | 10 pc               |
| Minimum order quantity               | 10 pc               |
| Sales key                            | AF6ZBX              |
| Product key                          | AF6ZBX              |
| Catalog page                         | Page 480 (C-2-2019) |
| GTIN                                 | 4055626032535       |
| Weight per piece (including packing) | 2.31 g              |
| Weight per piece (excluding packing) | 2.22 g              |
| Customs tariff number                | 39269097            |
| Country of origin                    | DE                  |

# QPD PSK 3/4X1,5 - Protective cap



1414724

<https://www.phoenixcontact.com/gb/products/1414724>

## Technical data

### Product properties

|                        |                |
|------------------------|----------------|
| Product type           | Protective cap |
| Product family         | QPD            |
| Type                   | QPD            |
| Retaining cord present | no             |
| Seal present           | no             |

### Dimensions

|        |         |
|--------|---------|
| Width  | 19.8 mm |
| Height | 36.5 mm |
| Length | 19.8 mm |

### Material specifications

|                         |         |
|-------------------------|---------|
| Material Protective cap | Plastic |
|-------------------------|---------|

### Environmental and real-life conditions

#### Ambient conditions

|                                         |                  |
|-----------------------------------------|------------------|
| Degree of protection                    | IP50             |
|                                         | IP50             |
| Ambient temperature (operation)         | -40 °C ... 80 °C |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |

# QPD PSK 3/4X1,5 - Protective cap



1414724

<https://www.phoenixcontact.com/gb/products/1414724>

## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1414724>



**DNV GL**

Approval ID: TAE00003J5

# QPD PSK 3/4X1,5 - Protective cap



1414724

<https://www.phoenixcontact.com/gb/products/1414724>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440208 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002314 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# QPD PSK 3/4X1,5 - Protective cap



1414724

<https://www.phoenixcontact.com/gb/products/1414724>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)