


Product data sheet

Specifications



Repacked Mounting box, New Unica, surface, 1 x 2 modules, anthracite

NU840254W



This repacked option saves 0.373 over the standard condition

Main

Range	New Unica
Device application	Mounting
Product or component type	Mounting box
Aesthetic name	Unica Pro
Number of modules	1 x 2 modules
Number of gangs	1 gang
fixing mode	Screws

Complementary

Device mounting	Surface
Cable entry	4 knock-outs
Material	ABS (acrylonitrile butadiene-styrene): box
Standards	IEC 60669-1 IEC 60884-1
Depth	40 mm
Width	87 mm
Height	87 mm
Product weight	0.05 kg
resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IK degree of protection	IK04
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	51.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	12 cm
Package 2 Width	18 cm
Package 2 Length	26 cm
Package 2 Weight	647 g
Unit Type of Package 3	S03
Number of Units in Package 3	40
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	3.033 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.4 kg CO2 eq.

Use Better



Materials and Substances

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Free of Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No