

00 21 21 HK S

Plumber's tool case 24 parts



- Strong tool case for professional use
- For extensive plumbing and installation work
- Equipped with 52 brand tools
- Flexible options due to the individual partitioning of the inserts in the 60 mm deep base tray and its cover plate with six large tool compartments
- Tough ratchet hinges hold the lid open where necessary despite the deadweight of the tools
- Two lockable steel flip locks protect the case contents from theft
- Tough and lightweight, rugged and distortion resistant
- Dimensions, interior (W x H x D): 460 x 310 x 190 mm
- 20 kg maximum load
- Rugged design made of ABS material, black
- Cover and tool plates made of Con-Pearl® material

Article No.	00 21 21 HK S
EAN	4003773050131
Net weight g	9600

technical change and errors excepted

Con-Pearl® is a registered trade mark of friedola TECH GmbH

Content 00 21 21 HK S (24)

Article No.			Quantity	Nominal size	
86 03 250	Knipex	Pliers Wrench, pliers and a wrench in a single tool	1		
87 01 250	Knipex	KNIPEX Cobra®, Hightech Water Pump Pliers	1	250 mm	
87 01 400	Knipex	KNIPEX Cobra® XL, Pipe Wrench and Water Pump Pliers	1		
74 06 180	Knipex	High Leverage Diagonal Cutter	1		
26 16 200	Knipex	Snipe Nose Side Cutting Pliers, (Stork Beak Pliers)	1	200 mm	
00 11 01	Knipex	KNIPEX TwinKey®, for all standard cabinets and shut-off systems	1		
006110	Wera	Screwdrivers for slotted screws, 160i	1	0,6 x 3,5 x 100 mm	
006120	Wera	Screwdrivers for slotted screws, 160i	1	1,0 x 5,5 x 125 mm	
006172	Wera	Screwdriver for Torx® screws, 167 i	1	TX15	
006174	Wera	Screwdriver for Torx® screws, 167 i	1	TX20	
006176	Wera	Screwdriver for Torx® screws, 167 i	1	TX25	
006152	Wera	Screwdrivers for cross recessed Phillips® screws, 162i PH	1	PH1 x 80 mm	
006154	Wera	Screwdrivers for cross recessed Phillips® screws, 162i PH	1	PH2 x 100 mm	
018266	Wera	Slotted chisel, 932 A	1	1,2 x 7,0 x 125	
018268	Wera	Slotted chisel, 932 A	1	1,6 x 9,0 x 150	
005655	Wera	Voltage detector, single-pole, 247	1	0,5 x 3,0 x 70 mm	
004018	Wera	8100 SA 8 Zyklop set of metal ratchets, 28 parts	1	1/4"	
003760	Wera	Joker open-end wrench	1	10 x 13 mm	
022086	Wera	set of hex key wrenches	1	1,5 - 10 mm	
90958	Heyco	Express key	1	17 x 19 mm; M 10	
16640003	Heyco	Safety cutter knife	1	18 mm	
101-0300	Picard	Locksmith's hammer	1	300 g	
340 250 1	Rennsteig	Mason's Chisels	1	250 mm	
02281	Stabila	spirit level type 70	1	30 cm	