



**Part Number :** [395300114](#)

**Product Description :** 5.08mm Pitch Eurostyle Horizontal Plug, with Standard Imprinting, Black, 14 Circuits

**Series Number :** 39530

**Status :** Active

**Product Category :** Terminal Blocks and Barrier Strip



---

## Documents & Resources

### Drawings

[395300114 sd.pdf](#)

### Specifications

[PS-39500-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39530
Description	5.08mm Pitch Eurostyle Horizontal Plug, with Standard Imprinting, Black, 14 Circuits
Application	Wire-to-Board
Comments	with Standard Imprinting
Component Type	Plug
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	822350532174

**Agency**

UL	E48521
----	--------

**Electrical**

Current - Maximum per Contact	18.0A
Voltage - Maximum	300V

**Physical**

Circuits (Loaded)	14
Color - Resin	Black
Entry Angle	Vertical
Lock to Mating Part	Yes
Number of Rows	1

Orientation	N/A
Panel Mount	No
PCB Retention	N/A
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	12, 14, 16, 18, 20, 22, 24, 26
Wire Size mm <sup>2</sup>	0.13-3.31

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

### Mates With / Use With

#### Mates with Part(s)

Description	Part Number
5.08mm Pitch Eurostyle Vertical PCB Headers	<u><a href="#">39531</a></u>
5.08mm Pitch Eurostyle Horizontal PCB Headers	<u><a href="#">39532</a></u>
5.08mm Pitch Eurostyle Dual Level PCB Headers	<u><a href="#">39538</a></u>
Mates With	Most 5.08mm Pitch Industry Standard PCB Headers