

## NT 30/1 ME CLASSIC

The NT 30/1 Me Classic is a practical and robust wet and dry vacuum cleaner. The 1,500 Watt machine features a 30-litre container and removes all kinds of dirt.



Order no. **1.428-572.0**

### Technical data

EAN code		4054278804200
Current type	Ph / V / Hz	1 / 220 - 240 / 50 - 60
Air flow	l/s	59
Vacuum	mbar / kPa	227 / 22.7
Container content	l	30
Container material		Stainless steel
Rated input power	W	max. 1500
Standard nominal width		ID 35
Cable length	m	6.5
Sound pressure level	dB(A)	78
Colour		silver
Weight incl. packaging	kg	9.8
Dimensions (L × W × H)	mm	375 × 360 × 645

### Equipment

Suction hose length	m	2.5
Suction hose type		with bend
Quantity of suction tubes	Piece(s)	2
Suction tubes length	mm	500
Suction tubes material		Metal
Quantity of filter bags	Piece(s)	1
Filter bag material		Fleece
Wet/dry floor nozzle width	mm	360
Crevice nozzle		■
Cartridge filter		PES
Stainless steel container		■

■ included in delivery.



## Compact, robust and mobile

- Excellent stability, easy manoeuvrability and convenient transport thanks to its slimline form and 4 castors.
- The bumper offers secure all-round protection for the vacuum cleaner and equipment.



## Excellent suction power

- NT Classic devices with a powerful 1,500 W turbine reliably remove a wide range of dirt.
- For excellent cleaning results.




## Service and comfort

- Sensationally fast: The Easy Service Concept allows removal of the turbine in just 44 seconds.
- The rapid turbine change not only saves an enormous amount of time, but also costs.

## EQUIPMENT FOR NT 30/1 ME CLASSIC

### 1.428-572.0



	Order no.	Description	
<b>CARTRIDGE FILTER, STANDARD, BIA C OR UP TO DUST CLASS M</b>			
<b>Cartridge filter paper</b>			
Cartridge filter	1 6.414-789.0	Paper cartridge filter with larger filter surface, standard for NT 48/1 and optional for NT 27/1/Me Advanced.	■
<b>Cartridge filter PES</b>			
Cartridge filter PES	2 2.885-891.0		■
<b>SUCTION NOZZLES</b>			
<b>All-purpose nozzles (wet/dry)</b>			
Floor tool replacement Edition	3 9.755-549.0		■
<b>Crevice nozzles</b>			
Crevice nozzle	4 9.770-638.0		■
<b>Car cleaning nozzles</b>			
Car nozzle, ID 35, 90 mm	5 6.906-108.0	Angled, flat, plastic car vacuuming tool with about 90 mm working width. Only for NT vacuum cleaners.	□
<b>FILTER BAGS</b>			
<b>Fleece filter bags (3 ply)</b>			
Paper filter bags, 10 Piece(s), NT 30/1	6 9.755-358.0		□
<b>OTHER ACCESSORIES FOR T AND NT</b>			
Drilling dust tool	7 2.679-000.0	Drilling dust nozzle for dust-free vacuuming. Suitable for dry and wet and dry vacuum cleaners from Kärcher.	□
CS 40 Me	8 2.863-026.0	The highly efficient CS 40 Me cyclone preseparator for all Kärcher wet and dry vacuum cleaners is a specially designed accessory for fine dust applications on construction sites or in industry.	□

■ Included in delivery. □ Available accessories.