




BULLDOG

Girder Clamps - Capacities 1 tonne to 10 tonnes




- Lightweight robust construction
- Durable baked enamel paint protection
- Super-quick adjustment to any girder within a range
- Spare parts always available



Product Code	Safe Working Load Kg	Adjustable Beam Width mm	A max. mm	B		C mm	D mm	E mm	F		G min. mm	H mm
				min. mm	max. mm				min. mm	min. mm		
LC1BD	1000	75 - 230	278	182	380	64	4	217	150	90	26	19
LC2BD	2000	75 - 230	278	182	380	74	6	217	150	90	26	21
LC3BD	3000	80 - 320	356	220	500	100	8	277	220	145	50	23
LC5BD	5000	90 - 320	356	220	500	112	10	277	220	145	47	29
LC10BD	10000	90 - 320	356	250	520	120	12	285	230	160	52	39

Adjustable Trolley



Product Code:	TRGC1BD	TRGC2BD	TRGC3BD	TRGC5BD	
Safe Working Load (kg)	1000	2000	3000	5000	
Clearance Dimensions (mm)	A	345	450	460	
	B	63-210	76-210	76-210	100-305
	C	30	39	47	57
	D	8	10	12	16
	E	238	276	324	350
	H	65-124	65-124	70-123	74-160
Beam width (mm)	63-210	76-210	76-210	100-305	
Net Weight (kg)	11	13	23	42	



PUSH GIRDER TROLLEYS

- Capacities 500 kg to 20 tonnes




Product Code	TR.5PBD	TR1PBD	TR2PBD	TR3PBD	TR5PBD	TR10PBD
Safe Working Load	500kg	1 t	2 t	3 t	5 t	10 t
Adjustable Beam Width mm	64 - 152	64 - 210	88 - 210	102 - 210	114 - 210	125 - 210
Clearance Dimensions	A	254	318	335	357	368
	B	216	260	300	345	395
	C	195	239	286	336	393
	H	110	135	161	185	220
Min. Radius Curve	m	.9	1.0	1.1	1.3	1.4
Net Weight	kg	8	14	21	36	51

- Lightweight robust construction
- Super-quick adjustment to any monorail
- Durable baked enamel paint protection
- Precision ball bearing trolley wheels



GEARED GIRDER TROLLEYS

- Capacities 500 kg to 20 tonnes



Product Code	TR1GBD	TR2GBD	TR3GBD	TR5GBD	TR10GBD
Safe Working Load	1 t	2 t	3 t	5 t	10 t
Adjustable Beam Width mm	64 - 210	88 - 210	102 - 210	114 - 210	125 - 210
Clearance Dimensions	A	380	390	513	430
	B	260	300	345	395
	C	239	286	336	393
	H	135	161	188	220
Min. Radius Curve	m	1.0	1.1	1.3	1.4
Net Weight	kg	18	27	43	60

- Lightweight robust construction
- Super-quick adjustment to any monorail
- Durable baked enamel paint protection
- Precision ball bearing trolley wheels

