



SD5760T Thunderbolt™ 4 Dual 4K Docking Station

Part Number: K34110EU | EAN Code: 5028252638555

Enhanced
productivity
today and in
the future.

If you need a high-speed dock that easily supports Dual 4K connections to HDMI monitors, powers as many devices as possible and reduces the number of adapters, cables and wired devices on your desktop, the SD5760T Thunderbolt 4 Dual 4K Docking Station is the ideal dock for you.

Perfect for busy professionals working in the home or office, this dock supports the latest MacBooks, Surface devices, and other Thunderbolt 4 enabled laptops with everything you need to enhance your productivity today and well into the future.

Providing a true plug-and-play experience, flexible video port options, 40Gbps data transfer speeds, dynamic Power Delivery and daisy chaining via Thunderbolt 4, the SD5760T offers everything you need in a docking station.


Features include:

- Supports Thunderbolt 4, Thunderbolt 3, USB4, and USB-C devices
- Transfers up to 40Gbps of data, video and audio
- Supports up to Single 8K @ 60Hz via a Thunderbolt 4 port when DSC is enabled or Dual 4K @ 60Hz via two HDMI ports.
- Supports up to 96W of Power Delivery and automatically adjusts for optimal performance
- 13-in-1 design includes Thunderbolt, USB-C, USB-A, HDMI, Ethernet, a combo audio jack, and micro and SD card readers


SD5760T Thunderbolt™ 4 Dual 4K Docking Station

Part Number: K34110EU | EAN Code: 5028252638555

Front




Back




SD5760T Thunderbolt™ 4 Dual 4K Docking Station

Part Number: K34110EU | EAN Code: 5028252638555



Universal Compatibility

Offers a quick and powerful plug-and-play solution for Thunderbolt 4, Thunderbolt 3, USB4 and USB-C devices running Windows (10 or later) or macOS (11 or later)



Thunderbolt™ 4 Technology

Transfer up to 40Gbps of data, video and audio (10Gbps for USB-C Gen2 laptops, 5Gbps for USB-C Gen1 laptops) through the included 0.8m (2.6') Thunderbolt 4 cable. Provides daisy chain support for SSDs, monitors and other Thunderbolt devices. Blocks peripheral devices from unauthorised access to your system memory using Intel VT-d DMA protection.



Single 8K or Dual 4K Support for Thunderbolt Devices

Extend visual productivity with the resolution, contrast and colour depth of Ultra HD. Supports up to Single 8K @ 60Hz via a Thunderbolt 4 port when DSC is enabled or Dual 4K @ 60Hz via 2 x HDMI ports.



Up to 96W Dynamic Power Delivery

Delivers power whenever and wherever you need it - to host and connected accessories. Supports up to 96W of Power Delivery and provides optimal performance under any usage scenario.



Productive 13-in-1 Design

Extend your productivity with 2 x HDMI ports, 1 x Thunderbolt 4 port, 1 x Thunderbolt 4 host port, 1 x USB-C 3.2 Gen2 10Gbps port, 2 x USB-A 3.2 Gen2 10Gbps ports, 2 x USB-A 3.2 Gen1 5Gbps ports, 1 x Gigabit Ethernet port, 1 x audio combo jack and UHS-II 4.0 SD/Micro SD card readers.



Zero-Footprint Mounting and Security Cable Lock Slots

Maximise desktop space and reduce cable clutter by mounting your docking station out of the way. Mounting bracket sold separately (K34050WW). Standard and Nano lock slots allow you to protect your investment with a Kensington cable lock (K65020EU or K65021WW), sold separately.

SD5760T Thunderbolt™ 4 Dual 4K Docking Station

Part Number: K34110EU | EAN Code: 5028252638555

System Requirements

Systems Supported	Supports Thunderbolt 4 / Thunderbolt 3 / USB4 and USB-C 3.2 devices
Operating Systems Supported	Windows® 10 or above macOS 11 or above
Plug & Play	Yes
Software	For Windows, need to enable Intel Thunderbolt™ software
System Resource Requirement	CPU: Intel® Core™ i5 6th generation or above Memory: 8Gb or above GPU: Intel® HD Graphics 620 or above
Additional Software Information	DockWorks compatible
USB-C Power Delivery	PD3.0: 5V, 9V, 15V/3A & 20V/4.8A (up to 96W Dynamic Power)

Docking Station

Technology	Intel® JHL8440 Thunderbolt 4 controller
------------	---

USB Interface

Type of USB Connector	Thunderbolt 4 / USB-C Connector
Host Connector	Supports Thunderbolt 4 / Thunderbolt 3 / USB4 / USB-C with full function

USB Connections

Ports	Front Panel : - 1 x Thunderbolt 4 Host Port (up to Dynamic PD 96W, 40Gbps) - 1 x Thunderbolt 4 DFP (up to PD 5V/3A, 40Gbps) - 2 x USB-A 3.2 Gen1 5Gbps (5V/0.9A) - 1 x SD/Micro SD 4.0 Card reader (UHS-II) - 1 x 3.5mm Audio combo Back Panel : - 1 x USB-C 3.2 Gen2 10Gbps (5V/1.5A) - 2 x USB-A 3.2 Gen2 10Gbps (5V/0.9A) - 2 x HDMI 2.0 - 1 x 1Gbps Ethernet
-------	--

Network Connections

Ethernet Port	RJ45
Compatible Ethernet Speeds	10/100/1000 Mbps

Host Connectivity

Host Docking Connector	Thunderbolt 4 upstream port PD up to 96W, Dynamic Power
------------------------	---

SD5760T Thunderbolt™ 4 Dual 4K Docking Station

Part Number: K34110EU | EAN Code: 5028252638555

Video Connections

Video Connectors				1 x Thunderbolt 4 2 x HDMI 2.0		
Maximum Resolution Supported				Please refer to table below		
	 ★ 		  + 		 ★ 	  + 
Thunderbolt™ 3 / Thunderbolt™ 4 / USB4 (Windows)	8K @ 60Hz*	4K @ 60Hz	4K @ 60Hz	Thunderbolt™ 3 / Thunderbolt™ 4 / USB4 (Windows)	4K up to 120Hz* or 1080p up to 240Hz*	1080p up to 240Hz
Thunderbolt™ 3 / Thunderbolt™ 4 / (macOS)	6K @ 60Hz	4K @ 60Hz	4K @ 60Hz			
USB-C Alt Mode (Windows)	4K @ 60Hz	4K @ 60Hz				
MacBook M1/M2 / iPad Pro	6K @ 60Hz	4K @ 60Hz				

* Support for Display Stream Compression (DSC) is based on the host device and monitor capabilities.



Audio Connections

Audio Connectors	1 x 3.5mm audio combo jack
------------------	----------------------------

LED Indicator

Blue LED	Power indicator
----------	-----------------

Material Specifications

Exterior	Enclosure: Aluminium / PC + ABS
Bottom	PC + ABS
Product Colour	Deep Space Grey / PMS Black

Other Features

Kensington Security Slot	Kensington Security Slot Kensington Nano Security Slot
VESA Mount Compatible	Yes, with K34050WW

Product Dimensions

Cable Dimensions	0.8m (31.5")
Unit Weight	0.36kg (0.79lbs)
Unit Dimensions without Peripherals	225 x 85 x 22mm (8.86 x 3.34 x 0.87")
Enclosure Colour & Material	Black PMS, PC+ABS with texture Deep Space Grey Aluminium
Desktop Footprint	191.25cm ² (27.92in ²)

SD5760T Thunderbolt™ 4 Dual 4K Docking Station

Part Number: K34110EU | EAN Code: 5028252638555

Packaging Dimensions

Packaging Style	Retail Package
Packaging Dimensions	242 x 108 x 100mm (9.53 x 4.25 x 3.94")
Packaging Weight	1.19kg (2.62lbs)
Packaging Content	1 x SD5760T Dock 1 x Thunderbolt 4 passive cable (0.8m) 1 x Power Supply Unit (135W) 1 x Instruction Guide 1 x Warranty Card 1 x Compliance Sheet 1 x Welcome card insert
Master Carton	6pcs

Power and Environmental

Power Adapter Rating	Input: 100-240V, AC 50/60Hz, 2A Output: 21V DC 6.4A (134.4W)
Relative Humidity	55% operating temperature @ 25°C (77°F)
Operating Temperature	0 to 45°C (32 to 113°F)
Storage Temperature	0 to 60°C (32 to 140°F)

Country of Origin, Regulatory and Warranty

Country of Origin	China
Certifications & Compliance	FCC, IC, CE, RCM, VCCI, UKCA, CB, RoHS, ACCO RSL
Warranty	3-Year Limited - worldwide



All specifications are subject to change without notice. Products may not be available in all markets. Kensington and the ACCO name and design are registered trademarks of ACCO Brands. Kensington The Professionals' Choice is a trademark of ACCO Brands. All other registered and unregistered trademarks are the property of their respective owners. Thunderbolt and the Thunderbolt logo are trademarks of Intel Corporation in the U.S. and/or other countries. © 2023 Kensington Computer Products Group, a division of ACCO Brands. All rights reserved. CBT41064EN

Kensington
The Professionals' Choice™

FOR MORE INFORMATION CONTACT: contact@kensington.com