





## ACCESSORIES

# PRODUCT-SPECIFIC ACCESSORIES



### FOR MULTIMETERS OR TESTERS WITH + TERMINAL ON TOP

Model	Description
	<b>Red test probe Ø 4 mm</b> P01103060Z removable for tester or DMM Use as "hands-free" test probe <ul style="list-style-type: none"> <li>• Male plug Ø 4 mm</li> <li>• 600 V CAT IV</li> </ul>




### FOR C.A 745 TESTER OR REMOTE-CONTROL PROBE

Model	Description
	<b>Red test probe Ø 4 mm</b> P01103061Z removable with locking pin For tester or remote-control probe <ul style="list-style-type: none"> <li>• Male plug Ø 4 mm</li> <li>• 600 V CAT IV</li> </ul>




### FOR C.A 704, C.A 740 & C.A 760 VOLTAGE ABSENCE TESTERS

Model	Description
	<b>Removable red test probe</b> P01103059Z <ul style="list-style-type: none"> <li>• Female plug Ø 4 mm</li> <li>• 600 V CAT IV</li> </ul>
	<b>Black test-probe lead</b> P01295464Z Insulated elbowed female plug Ø 4 mm Length 0.85 m <ul style="list-style-type: none"> <li>• 600 V CAT IV</li> </ul>

### FOR C.A 745N, C.A 755 AND C.A 757




Model	Description
	<b>Set of red/black test probes</b> P01102152Z <ul style="list-style-type: none"> <li>• CAT III/IV</li> </ul>
	<b>Set of red/black test probes</b> P01102153Z <ul style="list-style-type: none"> <li>• Ø 2 mm</li> <li>• CAT II</li> </ul>
	<b>Set of red/black test probes</b> P01102154Z <ul style="list-style-type: none"> <li>• Ø 4 mm</li> <li>• CAT II</li> </ul>




### FOR ALL VOLTAGE ABSENCE TESTERS, C.A 74X/XN SERIES / C.A 76X/XN SERIES

Model	Description
	<b>Set of 2 PVC IP2X leads</b> P01295463Z for C.A 760 and C.A 704 VATs Complies with NF C 18-510 and IEC 61010-031+A1:2008 <ul style="list-style-type: none"> <li>• IP2X test probe Ø 2 mm</li> <li>• Elbowed female plug Ø 4 mm</li> <li>• 15 A</li> <li>• 1.5 m</li> <li>• 600 V CAT IV</li> </ul>
	<b>Red removable test probe</b> P01102008Z <ul style="list-style-type: none"> <li>• Female plug Ø 4 mm</li> <li>• IEC 61243-3</li> </ul>
	<b>Black test-probe lead</b> P01102009Z Insulated elbowed female plug Ø 4 mm Length 0.85 m <ul style="list-style-type: none"> <li>• IEC 61243-3</li> </ul>

Model	Description
	<b>Set of 2 IP2X leads for C.A 740N and C.A 760N VATs</b> P01295462Z <ul style="list-style-type: none"> <li>• IP2X test probe Ø 4 mm</li> <li>• Elbowed female plug Ø 4 mm</li> <li>• 15 A</li> <li>• NF C 18-510 / IEC 61243-3 1000 V</li> <li>• 1.5 m</li> </ul>
	<b>Set of IP2X accessories for VAT</b> P01102121Z <ul style="list-style-type: none"> <li>• 2 x IP2X Ø 4 mm test probes</li> <li>• 1 point-point cable, L = 1.10 m</li> </ul>
	<b>C.A 751 measurement adapter</b> P01101997Z <ul style="list-style-type: none"> <li>• For 2P+E sockets</li> </ul>

### FOR C.A 771 & C.A 773 VOLTAGE ABSENCE TESTERS

Model	Description
	<b>Set of 2 red/black IP2X test probes Ø 4 mm</b> P01102128Z Female plug Ø 4 mm IEC 61423-3 1000 V
	<b>Set of 2 red/black IP2X test probes</b> P01102127Z Female plug Ø 4 mm 1000 V CAT IV
	<b>Set of 2 red/black test probes</b> P01102123Z Female plug Ø 4 mm 1000 V CAT IV

Model	Description
	<b>Set of 2 red/black test probes Ø 2 mm with crystal cap</b> P01102124Z Female plug Ø 4 mm IEC 61423-3 1000 V
	<b>Set of 2 red/black test probes Ø 4 mm</b> P01102125Z Female plug Ø 4 mm IEC 61423-3 1000 V
	<b>Crystal protective cap for test probe</b> P01102126Z