

SEALING PLUG 28X30 RD - Sealing plug



1421864

<https://www.phoenixcontact.com/gb/products/1421864>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sealing plug, color: red



Commercial data

Item number	1421864
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AF7DZX
Product key	AF7DZX
Catalog page	Page 707 (C-2-2019)
GTIN	4055626287645
Weight per piece (including packing)	9.65 g
Weight per piece (excluding packing)	9 g
Customs tariff number	39269097
Country of origin	DE

SEALING PLUG 28X30 RD - Sealing plug



1421864


<https://www.phoenixcontact.com/gb/products/1421864>

Technical data

Product properties

Product type	Sealing plugs
--------------	---------------

Dimensions

Dimensional drawing	
Length	30 mm
Diameter	27 mm

Material specifications

Material	PA
----------	----

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 100 °C
---------------------------------	-------------------

Mounting

Assembly note	The head of the sealing plug must still be visible after mounting in the screw connection (see "after mounting" photo).
---------------	---

SEALING PLUG 28X30 RD - Sealing plug


1421864

<https://www.phoenixcontact.com/gb/products/1421864>



Drawings

Dimensional drawing



Dimensional drawing

SEALING PLUG 28X30 RD - Sealing plug



1421864

<https://www.phoenixcontact.com/gb/products/1421864>

Classifications

ECLASS

ECLASS-13.0	23111190
-------------	----------

ETIM

ETIM 9.0	EC000032
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

SEALING PLUG 28X30 RD - Sealing plug



1421864
<https://www.phoenixcontact.com/gb/products/1421864>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk