

## TV/FM and Satellite Co-Axial Socket Outlets

NON ISOLATED  
FLUSH



K3520WHI



K3523WHI



K3525WHI



K3525D1WHI

ISOLATED  
FLUSH



K3521WHI



K3522WHI

## Grid Plus Frontplates



K3631GRA



K3632WHI



K3633GRA



K3634WHI



K3636WHI



K3638WHI



K3639WHI

**K3520WHI**  
SINGLE OUTLET  
**K3523WHI**  
TWIN OUTLET  
**K3525WHI**  
SINGLE F TYPE  
SATELLITE SOCKET  
**K3525D1WHI**  
TWIN F TYPE  
SATELLITE SOCKET

10

10

10

10

### MOUNTING BOXES:

FLUSH:  
861ZIC (25mm)

SURFACE:  
K2140WHI

Single outlet for connection to a single TV or FM co-axial aerial lead. Twin outlet for connection to each of two separate TV/FM, co-axial aerial leads.

DIMENSIONS: 86 x 86mm  
FIXING CENTRES: 60.3mm

BS 5733: 2010  
where applicable

BS 3041: 1977  
IEC 169-2: 1965

**K3521WHI**  
SINGLE OUTLET  
**K3522WHI**  
TWIN OUTLET  
WITH FM/TV DIPLEXER

10

10

### MOUNTING BOXES:

FLUSH:  
861ZIC (25mm)

SURFACE:  
K2140WHI

Provides safety isolation rated at 2000V a.c. between aerial lead and socket. Single outlet for connection to a single TV or FM co-axial aerial lead. Twin outlet with TV/FM diplexer for connection to single co-axial aerial lead with combined TV & FM signals.

DIMENSIONS: 86 x 86mm  
FIXING CENTRES: 60.3mm

BS 5733: 2010 where applicable  
BS 3041: 1977 IEC 169-2: 1965

**K3631WHI**  
**K3631GRA**  
1 MODULE  
**K3632WHI**  
**K3632GRA**  
2 MODULE  
**K3633WHI**  
**K3633GRA**  
3 MODULE  
**K3634WHI**  
**K3634GRA**  
4 MODULE

10

10

10

10

10

10

10

**K3636WHI**  
**K3636GRA**  
6 MODULE  
**K3638WHI**  
**K3638GRA**  
8 MODULE

1

1

1

1

**K3639WHI**  
12 MODULE

1

All modules from the Grid Plus range can be used with these frontplates.

### DIMENSIONS:

1 & 2 MODULE: 86 x 86mm  
3 & 4 MODULE: 86 x 146mm  
6 & 8 MODULE: 146 x 146mm  
12 MODULE: 206 x 146mm

BS 5733: 2010