

PRODUCT-DETAILS

## CR-P024AC2

### CR-P024AC2 Pluggable interface relay 2c/o, A1-A2=24VAC, 250V/8A



#### General Information

|                       |   |
|-----------------------|---|
| Extended Product Type | CR-P024AC2  |
| Product ID            | 1SVR405601R0000   |
| EAN                   | 4013614498220   |
| Catalog Description   | CR-P024AC2 Pluggable interface relay 2c/o, A1-A2=24VAC, 250V/8A   |
| Long Description      | The CR-P024AC2 pluggable interface relay is from the CR-P (pcb) relay range. This relay operates with a 24 V AC rated control supply voltage and has a 2 c/o (SPDT) output with contacts rated at 250 V / 8 A. Standard sockets, logic sockets, pluggable function modules, holder and marker are available as accessories. |

#### Ordering

|                        |          |
|------------------------|----------|
| Minimum Order Quantity | 10 piece |
| Customs Tariff Number  | 85364900 |

#### Popular Downloads

|                                   |                    |
|-----------------------------------|--------------------|
| Data Sheet, Technical Information | 2CDC110004C0210_05 |
| Instructions and Manuals          | 1SVC405600M9000    |

#### Dimensions

|                   |         |
|-------------------|---------|
| Product Net Width | 12.7 mm |
|-------------------|---------|

|                            |          |
|----------------------------|----------|
| Product Net Height         | 15.7 mm  |
| Product Net Depth / Length | 29 mm    |
| Product Net Weight         | 0.014 kg |

## Technical

|  |                                    |
|--|------------------------------------|
| Function                                       | Pluggable pcb interface relay CR-P |
| Sub-Function                                   | Relay w/o built in LED             |
| Output   | 2 c/o (SPDT) contacts              |
| Output Signal                                  | 250 V / 8 A                        |
| Rated Control Supply Voltage (U <sub>s</sub> ) | 24 V AC                            |

## Environmental

|             |                                   |
|-------------|-----------------------------------|
| RoHS Status | Following EU Directive 2011/65/EU |
|-------------|-----------------------------------|

## Certificates and Declarations (Document Number)

|                                 |                             |
|---------------------------------|-----------------------------|
| CCC Certificate                 | CCC_2007010303228779        |
| CSA Certificate                 | CSA_1587291                 |
| cUR Certificate                 | cUR_E244330                 |
| Declaration of Conformity - CCC | 2020970303000496            |
| Declaration of Conformity - CE  | No declaration needed       |
| EAC Certificate                 | EAC_RU_C-DE.ME77.B.00446-19 |
| Environmental Information       | 1SAA981009-2401             |
| Instructions and Manuals        | 1SVC405600M9000             |
| RMRS Certificate                | RMRS_1740019250             |
| RoHS Information                | 1SVD982031-0000             |
| UR Certificate                  | UR_E244330                  |
| VDE Certificate                 | VDE_40019129                |

## Container Information

|                                |               |
|--------------------------------|---------------|
| Package Level 1 Units          | box 10 piece  |
| Package Level 1 Width          | 332 mm        |
| Package Level 1 Height         | 28 mm         |
| Package Level 1 Depth / Length | 17 mm         |
| Package Level 1 Gross Weight   | 0.157 kg      |
| Package Level 1 EAN            | 4013614372995 |

## Classifications

|                            |                            |
|----------------------------|----------------------------|
| Object Classification Code | K                          |
| ETIM 4                     | EC001437 - Switching relay |
| ETIM 5                     | EC001437 - Switching relay |
| ETIM 6                     | EC001437 - Switching relay |
| ETIM 7                     | EC001437 - Switching relay |

|                    |                  |
|--------------------|------------------|
| eClass             | V11.0 : 27371601 |
| UNSPSC             | 39122331         |
| E-Number (Finland) | 2712739          |
| E-Number (Sweden)  | 4005307          |

---

## Categories

---

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Interface Relays and Optocouplers

