


Product datasheet

Specifications



MOUNTING PLATE NS3200 INS-INV2500 FIXED VERTICAL IN WIDTH 650

LVS03501

EAN Code: 3606481874641

Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
installation description	Cubicle - width 650 mm depth 400 mm Cubicle - width 650 mm depth 600 mm
Installed device	ComPact: fixed INS2000...2500 - control: direct front rotary handle - vertical installation ComPact: fixed INS630b...1600 - control: direct front rotary handle - vertical installation ComPact: fixed INV2000...2500 - control: direct front rotary handle - vertical installation ComPact: fixed INV630b...1600 - control: direct front rotary handle - vertical installation ComPact: fixed NS1600b - control: toggle - vertical installation ComPact: fixed NS2000...3200 - control: toggle - vertical installation
Poles description	1 x 3P: fixed INS2000...2500 vertical installation 1 x 4P: fixed INS2000...2500 vertical installation 1 x 3P: fixed INS630b...1600 vertical installation 1 x 4P: fixed INS630b...1600 vertical installation 1 x 3P: fixed INV2000...2500 vertical installation 1 x 4P: fixed INV2000...2500 vertical installation 1 x 3P: fixed INV630b...1600 vertical installation 1 x 4P: fixed INV630b...1600 vertical installation 1 x 3P: fixed NS1600b vertical installation 1 x 4P: fixed NS1600b vertical installation 1 x 3P: fixed NS2000...3200 vertical installation 1 x 4P: fixed NS2000...3200 vertical installation
Number of vertical modules [50 mm]	16 module(s): INS2000...2500, front connection on adaptor in 650 mm Widecubicle 16 module(s): INS2000...2500, rear connection on adaptor in 650 mm Widecubicle 14 module(s): INS630b...1600, front connection on adaptor in 650 mm Widecubicle 16 module(s): INV2000...2500, front connection on adaptor in 650 mm Widecubicle 16 module(s): INV2000...2500, rear connection on adaptor in 650 mm Widecubicle 14 module(s): INV630b...1600, front connection on adaptor in 650 mm Widecubicle 14 module(s): NS1600b, front connection on adaptor in 650 mm Widecubicle 16 module(s): NS2000...3200, front connection on adaptor in 650 mm Widecubicle
Standards	IEC 61439-2
Product certifications	ASTA

Complementary

Material	Sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	White (RAL 9003)
Width	650 mm
Height	200 mm
Net weight	2.9 kg
Functional unit	650 mm 400 mm PrismaSeT P cubicle ComPact INS2000...2500 fixed direct front rotary handle vertical 3P 1 front connection on adaptor 16 262.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INS2000...2500 fixed direct front rotary handle vertical 4P 1 front connection on adaptor 16 262.5 mm 650 mm 600 mm PrismaSeT P cubicle ComPact INS2000...2500 fixed direct front rotary handle vertical 3P 1 rear connection on adaptor 16 262.5 mm 650 mm 600 mm PrismaSeT P cubicle ComPact INS2000...2500 fixed direct front rotary handle vertical 4P 1 rear connection on adaptor 16 262.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INS630b...1600 fixed direct front rotary handle vertical 3P 1 front connection on adaptor 14 262.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INS630b...1600 fixed direct front rotary handle vertical 4P 1 front connection on adaptor 14 262.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INV2000...2500 fixed direct front rotary handle vertical 3P 1 front connection on adaptor 16 262.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INV2000...2500 fixed direct front rotary handle vertical 4P 1 front connection on adaptor 16 262.5 mm 650 mm 600 mm PrismaSeT P cubicle ComPact INV2000...2500 fixed direct front rotary handle vertical 3P 1 rear connection on adaptor 16 262.5 mm 650 mm 600 mm PrismaSeT P cubicle ComPact INV2000...2500 fixed direct front rotary handle vertical 4P 1 rear connection on adaptor 16 262.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INV630b...1600 fixed direct front rotary handle vertical 3P 1 front connection on adaptor 14 262.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INV630b...1600 fixed direct front rotary handle vertical 4P 1 front connection on adaptor 14 262.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NS1600b fixed toggle vertical 3P 1 front connection on adaptor 14 212.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NS1600b fixed toggle vertical 4P 1 front connection on adaptor 14 212.5 mm 650 mm 600 mm PrismaSeT P cubicle ComPact NS2000...3200 fixed toggle vertical 3P 1 front connection on adaptor 16 212.5 mm 650 mm 600 mm PrismaSeT P cubicle ComPact NS2000...3200 fixed toggle vertical 4P 1 front connection on adaptor 16 212.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	20 cm
Package 1 Length	58 cm
Package 1 Weight	2.944 kg
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	18.25 kg

Logistical informations

Country of origin	IN
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	4758f26b-dbf8-498a-a5c2-4de140d6aa9a
REACH Regulation	REACH Declaration
Halogen content performance	Halogen free plastic parts product
PVC free	Yes

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions

